





REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
A		INITIAL RELEASE	09APR2015	RGV TB
B		REV PER ECN-22-188128	09DEC2022	JMS BK
B1		REV PER ECN-23-213534	02JUN2023	JMS BDK
E		REV PER ECN-23-224389	01AUG2023	JMS BDK



- 8.4mm² CONDUCTOR. CURRENT RATING DEPENDS UPON CONDUCTOR SIZE. KEEP TERMINALS BELOW 150°C MAXIMUM CONTINUOUS.
- 3 MINUTES @ +40°C AMBIENT WITH 8.4mm² (#8AWG) CONDUCTOR.
- A COIL ECONOMIZER CIRCUIT IS NEEDED IF COIL IS ENERGIZED FOR AN EXTENDED LENGTH OF TIME AT A HIGH OPERATING TEMPERATURE (I.E. 85°C).



NO	120mm	2138602-2
YES	153mm	2138602-1
STRIPPED WIRE \triangle 4, REF	WIRE LENGTH "L"	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. VESTAL 09APR2015	TE Connectivity	
DIMENSIONS: INCHES [mm]		CHK T. BANAS 09APR2015	NAME EVC135 RELAY, WITH 24VDC COIL	
		APVD T. BANAS 09APR2015	PRODUCT SPEC	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC		
0 PLC ±		SIZE		
1 PLC ±.012[0.3]		CAGE CODE		
2 PLC ±.005[0.13]		DRAWING NO		
3 PLC ±		RESTRICTED TO		
4 PLC ±		A2		
ANGLES ±1		SCALE 1:1		
FINISH		SHEET 1 OF 1		
MATERIAL		REV E		
		CUSTOMER DRAWING		