



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	I	FIRST DRAFT	16MAY2012	MBH	MDB
	A	RELEASED PER ECO-13-000735	14JAN2013	DLD	MDB
	AI	REVISED PER ECO-13-005998	05APR2013	DLD	SLM
	B	REV PER ECN-23-199890	24FEB2023	JMS	LM



SCALE 5:1



- FOR INSULATION $\varnothing 1.4$ TO $\varnothing 1.8$ mm.
- PARTS MUST BE THOROUGHLY MIXED TO ASSURE PROPER COATING OF APPLIED LUBRICANT PRIOR TO APPLICATION.
- MATERIAL: VAMAC
COLOR: BLACK
- INSULATION CRIMP MEASUREMENTS ARE DEPENDENT ON WIRE INSULATION TYPE AND OUTSIDE DIAMETER. INSULATION CRIMP MUST BE SUFFICIENT TO KEEP SEAL FROM SLIDING OUT OF CRIMP WHEN INSERTING INTO CONNECTOR CAVITY BUT NOT TEAR THE SEAL.

2138898-1

PART NO.

© 2023 TE Connectivity. All Rights Reserved.

DIMENSIONS: mm		DWN M. HITCHCOCK	16MAY2012	MATERIAL	-	FINISH	-
TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK M.D. BROWN	16MAY2012				
		APVD M.D. BROWN	16MAY2012				
0 PLC ±-		PRODUCT SPEC		NAME MCON CABLE SEAL, 50 DURO-METER SILO 3.45 - 3.70mm DIAMETER			
1 PLC ±-		-		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
2 PLC ±-		APPLICATION SPEC		A 4	00779	C-2138898	-
3 PLC ±-		-					
4 PLC ±-		WEIGHT					
ANGLES ±1°		-		CUSTOMER DRAWING			
		-		SCALE	10:1	SHEET	1 OF 1
				REV B			