

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	4MAR2015	D.S	F.Y
	B	PER ECO-15-003626	9MAR2015	D.S	F.Y

NOTES, UNLESS OTHERWISE SPECIFIED,

1. MATERIALS:

HOUSING: LCP, GLASS FILLED, UL94-V0, BLACK.

CONTACT: COPPER ALLOY

2. 0.00076mm MIN GOLD AT CONTACT AREA;

0.00254mm MIN TIN PLATING AT PRESS-FIT AREA

0.00127mm MIN NICKEL OVERALL AS UNDERPLATE.






3. PRINT PART NUMBER AND DATE CODE AT APPROXIMATE AREA.

4. KEEP OUT ZONE FROM OTHER COMPONENTS.

5. MINIMUM BOARD THICKNESS: 1.60mm.

6. FINISHED HOLE SIZE: 0.725±0.075mm, COPPER PLATE:0.03~0.07mm

TIN PLATE: 0.007~0.02mm.RECOMMEND DRILL HOLE SIZE:Ø0.838mm



RECOMMENDED PCB LAYOUT
COMPONENT SIDE SHOWN

2169862-1
PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN JEFF GONG 09-Mar-15

CHK SANDERS YAN 03-Sep-12

APVD Alex Cai 03-Sep-12

PRODUCT SPEC

108-2473

APPLICATION SPEC

WEIGHT

-

Customer Drawing



TE Connectivity

IMPACT POWER 6PAIR
VERTICAL RECEPTACLE
PRESS FIT

SIZE CAGE CODE DRAWING NO RESTRICTED TO


A300779C-2169862

SCALE 2:1

SHEET 1 OF 1

REV B

DIMENSIONS:
mm



TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±
2 PLC ±0.25
3 PLC ±
4 PLC ±
ANGLES ±3°

MATERIAL

-

FINISH

-