

1. ASSEMBLY TESTED FOR CONTINUITY, OPENS, SHORTS, EEPROM PROGRAM AND SIGNAL INTEGRITY.
2. ROHS AND REACH COMPLIANCE: PRODUCT AND PROCESSING MEETS REQUIREMENTS OF TE SPECIFICATION TEC-138-702.

△3 LABEL INFORMATION:

TE	2163487-[]	TE LOGO AND P/N
---	METERS	LENGTH
YYWW		DATE CODE
MADE IN	---	COUNTRY OF ORIGIN

△4 LABEL INFORMATION:


TE	2163487-[]	TE LOGO AND P/N
MINI-SAS HD		
YYWWSSSS		YYWW= DATE CODE, SSSS= SERIAL NUMBER
		BARCODE

5. MINI-SAS HD EEPROM PROGRAMMED PER 2163487_EEPROM.

△6 -1 ONLY: LABEL IS APPLIED TO THE CENTER OF CABLE ASSEMBLY.

7 +0.10 -0	METERS	2163487-8
6 +0.10 -0	METERS	2163487-7
5 +0.10 -0	METERS	2163487-6
4 +0.08 -0	METERS	2163487-5
3 +0.08 -0	METERS	2163487-4
2 +0.08 -0	METERS	2163487-3
1 +0.08 -0	METERS	2163487-2
0.5 +0.05 -0	METERS	2163487-1 △6
L		PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN P.LI 09MAR2012	TE Connectivity	
DIMENSIONS: mm		CHK J.MEYERS 09MAR2012	NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD J.MEYERS 09MAR2012	CABLE ASSEMBLY, 26 AWG INFINITWIST MINI-SAS HD, 4X TO MINI-SAS, 4X	
0. PLC ± -		PRODUCT SPEC	APPLICATION SPEC	
1. PLC ± -			SIZE CASE CODE DRAWING NO	
2. PLC ± -			RESTRICTED TO	
3. PLC ± -			A1 00779 C=2163487	
4. PLC ± -			WEIGHT	
ANGLES ± -			CUSTOMER DRAWING	
MATERIAL	FINISH		SCALE 1:1	SHEET 1 OF 2
				REV C



THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN	09MAR2012	STE TE Connectivity
		CHK	09MAR2012	
		APVD	09MAR2012	NAME CABLE ASSEMBLY, 26 AWG INFINITWIST MINI-SAS HD, 4X TO MINI-SAS, 4X
		PRODUCT SPEC		
		APPLICATION SPEC		SIZE A1
		WEIGHT		
MATERIAL		FINISH		RESTRICTED TO
		CUSTOMER DRAWING	SCALE 1:1	SHEET 2 OF 2