






LOC	DIST	REVISIONS					
GP	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			A	PRODUCTION RELEASE	29FEB2016	JW	SH


- ⚠ MATERIAL:
CAGE - 0.25mm THICK NICKEL SILVER ALLOY
HEATSINK - ALUMINUM
HEATSINK CLIP - STAINLESS STEEL
EMI SPRING(S) - COPPER ALLOY
- ⚠ FINISH:
HEATSINK - ELECTROLESS NICKEL
HEATSINK CLIP - PASSIVATE
EMI SPRING(S) - 0.8um MIN MATTE TIN OVER 0.8um MIN NICKEL,
NON-PLATED EDGES PERMISSIBLE.
3. MATES WITH SFP MSA COMPLIANT TRANSCEIVERS.
- ⚠ PADS AND VIAS CHASSIS GROUND.
- ⚠ DATUM AND BASIC DIMENSION ESTABLISHED BY CUSTOMER.
6. MINIMUM PC BOARD THICKNESS:
SINGLE SIDED = 1.50mm
DOUBLE SIDED = 3.00mm
- ⚠ REFERENCE APPLICATION SPEC. 114-13120, HOLE A, FOR
RECOMMENDED DRILL HOLE DIAMETER AND PLATING THICKNESS.




SCALE 3:1






- ⚠ REFERENCE APPLICATION SPEC. 114-13120, HOLE C, FOR
RECOMMENDED DRILL HOLE DIAMETER AND PLATING THICKNESS.
- ⚠ DIMENSION APPLIES PRIOR TO INSERTION OF SFP MODULE.
10. CAGE ASSEMBLY, HEATSINK CLIP AND HEATSINK SHIPPED
ASSEMBLED.



13.5	2170170-1
H MAX	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D.ZHU	30NOV2011	 TE Connectivity		
DIMENSIONS:		CHK A.CAI	30NOV2011			
mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	SFP+ 1X1 CAGE ASSEMBLY, PRESS-FIT PRESS-FIT, EMI SPRINGS WITH HEATSINK	
		0 PLC ±0.1	1 PLC ±0.1			
		2 PLC ±0.1	3 PLC ±0.05	PRODUCT SPEC	SIZE	
		4 PLC ±0.05	ANGLES ±0.05			
MATERIAL		FINISH		DRAWING NO		RESTRICTED TO
				A100779C=2170170		
				CUSTOMER DRAWING		
					SCALE 2:1 SHEET 1 OF 2 REV A	

LOC		DIST		REVISIONS			
GP		00		P	LTR	DESCRIPTION	DATE
						SEE SHEET 1	



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	D.ZHU	30NOV2011	TE Connectivity		
		CHK	D.ZHU	30NOV2011			
		APVD	A.CAI	30NOV2011	NAME		
DIMENSIONS:		PRODUCT SPEC			SFP+ 1XI CAGE ASSEMBLY, PRESS-FIT		
mm		108-2364			PRESS-FIT, EMI SPRINGS		
		APPLICATION SPEC			WITH HEATSINK		
		114-13120			SIZE		
MATERIAL		WEIGHT			A100779C=2170170		
		CUSTOMER DRAWING			RESTRICTED TO		
					SCALE		
					2:1		
					SHEET		
					2 of 2		
					REV		
					A		