






LOC	DIST	REVISIONS					
GP	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			A	INITIAL RELEASE	21FEB2012	JY	CW
			B	REVISED PER ECO-14-000886	20FEB2013	JW	SH
			B1	REVISED PER ECO-14-010419	11JUL2014	JW	SH
			C	REVISED PER ECO-15-013594	25SEP2015	JW	SH



- 1 DATUM AND BASIC DIMENSION TO BE DETERMINED BY CUSTOMER.
- 2 INTERPRETATION OF DATUM REFERENCE FRAME IN ACCORDANCE WITH SECT 4.4.1.1 OF ASME Y14.5M-1994.
- 3 TOP OF PT CONNECTOR TO BE 0-0.15 FROM INSIDE SURFACE OF SPRING PLATE.
- 4 COPPER ALLOY.
- 5 1.25um MINIMUM TIN PER ASTM B545 OVER NICKEL FLASH PER QQ-N-290. NON-PLATED EDGES PERMISSIBLE.
- 6 LCP, HIGH TEMPERATURE, UL 94V-0 RATED, BLACK.
- 7 POLYESTER, UL 94V-0 RATED, BLACK.
- 8 CONTACT MATING AREA: SURFACE TREATMENT OVER 0.76um MINIMUM GOLD PER ASTM B488 OVER 1.27um MINIMUM NICKEL PER QQ-N-290. NEEDLE EYE: 1.25um MINIMUM TIN PER ASTM B545 OVER 1.25um MINIMUM NICKEL PER QQ-N-290. REMAINDER OF CONTACT: 0.76um MINIMUM NICKEL PER QQ-N-290.
9. NON-PLATED EDGES ARE PERMISSIBLE.
- 10 DATE CODE AND PART NUMBER IN APPROXIMATE LOCATION SHOWN
- 11 NICKEL SILVER ALLOY(NO PLATING)



TOP VIEW
SCALE 2:1

SUPERSEDED BY: 2170305-2	8	4, 6, 7	NO	1	2170305-2
	8	4, 6, 1	5	4	2170305-1
CONNECTOR FINISH		CONNECTOR MATERIAL	CAGE FINISH	CAGE MATERIAL	PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: JASON YANG 21FEB2012 CHK: ALEX CAI 21FEB2012 APVD: ALEX CAI 21FEB2012	TE Connectivity		
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ±0.1 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±1°	NAME CAGE ASSEMBLY AND PT CONNECTOR ASSEMBLY, PRESS FIT, 1X6, SFP		
MATERIAL SEE NOTES		SEE NOTES	SIZE A1	CAGE CODE 00779	DRAWING NO 2170305
		Customer Drawing	SCALE 3:1	SHEET 1	REV C

