





THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION  
 © COPYRIGHT - By - ALL RIGHTS RESERVED.


LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION		DATE	DWN	APVD	
	A	INITIAL RELEASE		22NOV2013	SY	FY	

NOTES:

- ⚠ MATERIAL CONTACTS; PHOSPHORBRONZE
- ⚠ MATERIAL HOUSING; GLASSFILLED POLYESTER (GRAY)
- ⚠ GENERAL PLATING SPECIFICATION: UNDERPLATING (ENTIRE CONTACT): 1,27µm NICKEL MIN. AND COMPLIANT PIN SECTION: 0,5µm TIN-LEAD MIN. FOR PLATING OF MATING SURFACES SEE APPLICABLE SPECIFICATION REFERENCE FOR EACH DASH NUMBER.
- ⚠ CONFORMS TO ALL TESTING ACCORDING IEC 61076-4-101 PERFORMANCE LEVEL 2.
- ⚠ CONFORMS TO ALL TESTING ACCORDING IEC 61076-4-101 PERFORMANCE LEVEL 1.
- ⚠ CONNECTOR TESTED AND QUALIFIED AGAINST TELCORDIA GR-1217-CORE QUALITY LEVEL III, CENTRAL OFFICE APPLICATIONS.
- ⚠ CONNECTOR LUBRICATED WITH TELCORDIAGR-1217-CORE APPROVED LUBRICANT.
- ⚠ ASSEMBLY PRINTED WITH P/N AND DATECODE
- ⚠ THE MARKING CAN APPEAR ON THE FRONT SIDE OR BACK SIDE.
- ⚠ HOLE PATTERN FOR FEMALE CONNECTOR TYPE A
- ⚠ 110 PLATED-THROUGH HOLES AT 2x2mm SQUARE GRID
- ⚠ ROW "r" 13 PLATED THROUGH HOLES FOR UPERSHIELD
- ⚠ SHIELD MOUNTED ON CONNECTOR WITH DOUBLE SIDED ADHESIVE TAPE OR ADHESIVE.
- ⚠ AREA RESERVED FOR KEYING PART (BASIC P.N. 100526)
- ⚠ 13 BASIC P.N. LOWERSHIELD: 5338108



COMPONENT SIDE AS SHOWN  
 RECOMMENDED PCB-HOLE LAY-OUT



SCALE 2,5:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN SANDERS YAN 22NOV2013
DIMENSIONS: mm		CHK -
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD FRANK YANG 22NOV2013
6-PLG ±		NAME
1-PLG ±		108-19082
2-PLG ±		APPLICATION SPEC
3-PLG ±		114-19029
4-PLG ±		WEIGHT -
ANGLES ±		FINISH -
MATERIAL -		SCALE 5:1

FINISH	MATERIAL	2170862-1
PARTNUMBER		
TE Connectivity		
Z-PACK 2mm HM		
TYPE A - 25 COLUMNS		
PRE-SHIELDED RECEPTACLE		
SIZE A2	CAGE CODE 00779	DRAWING NO C=2170862
CUSTOMER DRAWING		RESTRICTED TO -
SHEET 1 of 1		REV A