





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
H	—		B1	REVISED PER ECN-25-306161	13FEB2025	MK	GC


SECTION A-A



- NOTES:
- 1 MATERIAL CONTACTS; PHOSPHORBRONZE
 - 2 MATERIAL HOUSING; GLASSFILLED POLYESTER (GRAY)
 - 3 GENERAL PLATING SPECIFICATION: UNDERPLATING (ENTIRE CONTACT): 1,27µm NICKEL MIN. AND COMPLIANT PIN SECTION: 0,5µm TIN-LEAD MIN. FOR PLATING OF MATING SURFACES SEE APPLICABLE SPECIFICATION REFERENCE FOR EACH DASH NUMBER.
 - 3 CONFORMS TO ALL TESTING ACCORDING IEC 61076-4-101 PERFORMANCE LEVEL 2.
 - 4 CONFORMS TO ALL TESTING ACCORDING IEC 61076-4-101 PERFORMANCE LEVEL 1.
 - 5 CONNECTOR TESTED AND QUALIFIED AGAINST TELCORDIA GR-1217-CORE QUALITY LEVEL III, CENTRAL OFFICE APPLICATIONS.
 - 6 CONNECTOR LUBRICATED WITH TELCORDIA GR-1217-CORE APPROVED LUBRICANT.
 - 8 ASSEMBLY PRINTED WITH P/N AND DATECODE
 - 9 THE MARKING CAN APPEAR ON THE FRONT SIDE OR BACK SIDE.
 - 10 HOLE PATTERN FOR FEMALE CONNECTOR TYPE B-22 COLUMNS
 - 11 110 PLATED-THROUGH HOLES AT 2x2mm SQUARE GRID
 - 11 ROW "f" 11 PLATED THROUGH HOLES FOR UPPERSHIELD
 - 11 SHIELD MOUNTED ON CONNECTOR WITH DOUBLE SIDED ADHESIVE TAPE OR ADHESIVE.
 - 12 BASIC P.N. LOWERSHIELD : 352468 OR 5352468.



COMPONENT SIDE AS SHOWN
RECOMMENDED PCB-HOLE LAY-OUT
SCALE 2,5:1



P.C.B. HOLE DIM. COMPLIANT PIN
FOR DETAILS SEE
APPLICATION SPECIFICATION

THIS DRAWING IS A CONTROLLED DOCUMENT.		FINISH		MATERIAL		2170863-1	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PARTNUMBER		TE Connectivity	
MATERIAL		FINISH		Z-PACK 2mm HM TYPE B - 22 COLUMNS PRE-SHIELDED RECEPTACLE		RESTRICTED TO	
DWN SANDERS YAN		25NOV2013		NAME		SIZE	
CHK -		25NOV2013		APVD FRANK YANG		CAGE CODE	
PRODUCT SPEC		108-19082		DRAWING NO		REV	
APPLICATION SPEC		114-19029		WEIGHT		SCALE	
CUSTOMER DRAWING		5:1		SHEET		1 OF 1	