



REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	NEW DRAWING	21MAY2018	GCM	AP
	A1	PCB LAYOUT AND SCHEDULE ADDED	24JAN2023	DM	AP



RECOMMENDED PCB LAYOUT PLAN




TYPE	a (mm)	b (mm)	c (mm)
1206	1.90 to 2.10	4.10 to 4.30	1.50 to 1.70

NOTES:

- 1. FOR FURTHER INFORMATION SEE DATA SHEET FOR CRGCQ SERIES SMD AEC-Q200 THICK FILM CHIP RESISTORS

RoHS Compliant



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	21MAY2018						
		CHK	21MAY2018						
		APVD	21MAY2018						
		ALLAN.P	ALLAN.P						
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME SMD AEC-Q200 COMPLIANT THICK FILM CHIP RESISTOR TYPE CRGCQ 1206 SERIES					
		0 PLC	±0.5		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
		1 PLC	±0.2		A3	00779	©=2176344	-	
		2 PLC	±0.1		CUSTOMER DRAWING				
		3 PLC	±		SCALE	SHEET		REV	
		4 PLC	±		40:1	1 OF 2		A1	
		ANGLES	±5°						
MATERIAL		FINISH							
-		-							

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-


SCHEDULE

TCPN	CATALOGUE NUMBER	PART DESCRIPTION	PART STATUS
2176344-1	CRGCQ1206J1R0	CRGCQ 1206 1R0 5%	PRODUCTION
2176344-2	CRGCQ1206J1R5	CRGCQ 1206 1R5 5%	PRODUCTION
2176344-3	CRGCQ1206J2R2	CRGCQ 1206 2R2 5%	PRODUCTION
2176344-4	CRGCQ1206J3R3	CRGCQ 1206 3R3 5%	PRODUCTION
2176344-5	CRGCQ1206J4R7	CRGCQ 1206 4R7 5%	PRODUCTION
2176344-6	CRGCQ1206J6R8	CRGCQ 1206 6R8 5%	PRODUCTION
2176344-7	CRGCQ1206J10R	CRGCQ 1206 10R 5%	PRODUCTION
2176344-8	CRGCQ1206J15R	CRGCQ 1206 15R 5%	PRODUCTION
2176344-9	CRGCQ1206J22R	CRGCQ 1206 22R 5%	PRODUCTION
1-2176344-0	CRGCQ1206J33R	CRGCQ 1206 33R 5%	PRODUCTION
1-2176344-1	CRGCQ1206J47R	CRGCQ 1206 47R 5%	PRODUCTION
1-2176344-2	CRGCQ1206J68R	CRGCQ 1206 68R 5%	PRODUCTION
1-2176344-3	CRGCQ1206J100R	CRGCQ 1206 100R 5%	PRODUCTION
1-2176344-4	CRGCQ1206J150R	CRGCQ 1206 150R 5%	PRODUCTION
1-2176344-5	CRGCQ1206J220R	CRGCQ 1206 220R 5%	PRODUCTION
1-2176344-6	CRGCQ1206J330R	CRGCQ 1206 330R 5%	PRODUCTION
1-2176344-7	CRGCQ1206J470R	CRGCQ 1206 470R 5%	PRODUCTION
1-2176344-8	CRGCQ1206J680R	CRGCQ 1206 680R 5%	PRODUCTION
1-2176344-9	CRGCQ1206J1K0	CRGCQ 1206 1K0 5%	PRODUCTION
2-2176344-0	CRGCQ1206J1K5	CRGCQ 1206 1K5 5%	PRODUCTION
2-2176344-1	CRGCQ1206J2K2	CRGCQ 1206 2K2 5%	PRODUCTION
2-2176344-2	CRGCQ1206J3K3	CRGCQ 1206 3K3 5%	PRODUCTION
2-2176344-3	CRGCQ1206J4K7	CRGCQ 1206 4K7 5%	PRODUCTION
2-2176344-4	CRGCQ1206J6K8	CRGCQ 1206 6K8 5%	PRODUCTION
2-2176344-5	CRGCQ1206J10K	CRGCQ 1206 10K 5%	PRODUCTION
2-2176344-6	CRGCQ1206J15K	CRGCQ 1206 15K 5%	PRODUCTION
2-2176344-7	CRGCQ1206J22K	CRGCQ 1206 22K 5%	PRODUCTION
2-2176344-8	CRGCQ1206J33K	CRGCQ 1206 33K 5%	PRODUCTION
2-2176344-9	CRGCQ1206J47K	CRGCQ 1206 47K 5%	PRODUCTION
3-2176344-0	CRGCQ1206J68K	CRGCQ 1206 68K 5%	PRODUCTION

SCHEDULE

TCPN	CATALOGUE NUMBER	PART DESCRIPTION	PART STATUS
3-2176344-1	CRGCQ1206J100K	CRGCQ 1206 100K 5%	PRODUCTION
3-2176344-2	CRGCQ1206J150K	CRGCQ 1206 150K 5%	PRODUCTION
3-2176344-3	CRGCQ1206J220K	CRGCQ 1206 220K 5%	PRODUCTION
3-2176344-4	CRGCQ1206J330K	CRGCQ 1206 330K 5%	PRODUCTION
3-2176344-5	CRGCQ1206J470K	CRGCQ 1206 470K 5%	PRODUCTION
3-2176344-6	CRGCQ1206J680K	CRGCQ 1206 680K 5%	PRODUCTION
3-2176344-7	CRGCQ1206J1M0	CRGCQ 1206 1M0 5%	PRODUCTION
3-2176344-8	CRGCQ1206J1M5	CRGCQ 1206 1M5 5%	PRODUCTION
3-2176344-9	CRGCQ1206J2M2	CRGCQ 1206 2M2 5%	PRODUCTION
4-2176344-0	CRGCQ1206J3M3	CRGCQ 1206 3M3 5%	PRODUCTION
4-2176344-1	CRGCQ1206J4M7	CRGCQ 1206 4M7 5%	PRODUCTION
4-2176344-2	CRGCQ1206J6M8	CRGCQ 1206 6M8 5%	PRODUCTION
4-2176344-3	CRGCQ1206J10M	CRGCQ 1206 10M 5%	PRODUCTION
4-2176344-4	CRGCQ1206ZR	CRGCQ 1206 ZEROHM	PRODUCTION

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ±0.5 1 PLC ±0.2 2 PLC ±0.1 3 PLC ± 4 PLC ± ANGLES ±°
MATERIAL	FINISH
-	-

DWN	21MAY2018
CHK	21MAY2018
APVD	21MAY2018
PRODUCT SPEC	-
APPLICATION SPEC	-
WEIGHT	-

		TE Connectivity	
		NAME	
SMD AEC-Q200 COMPLIANT THICK FILM CHIP RESISTOR TYPE CRGCQ 1206 SERIES		RESTRICTED TO	
SIZE	CAGE CODE	DRAWING NO	
A3	00779	©=2176344	-