

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20








ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	ECR-13-009111	04JUN2013	WJ	DH
	AI	ECR-13-013822	02SEP2013	JvH	DH



SECTION C-C

TE PN: 2173157-2

TE PN FOR LOW MOQ: 2173157-3

NOTES:


1 VERSION: XX, PRODUCTION DATE: YWWD, SHIFT CODE: S,
PRODUCTION LINE NO: L.

2 COPLANARITY OF 11 SOLDER SURFACES 0,08 MAX.

3 PICK AND PLACE AREA Ø3

4	SLEEVE	LCP	
3	SHELL	STAINLESS STEEL	Tin over Nickel plating
2	CONTACT	COPPER ALLOY	Gold over Nickel plating
1	HOUSING	LCP	
ITEM NO.	DESCRIPTION	MATERIAL	FINISH

DWN	17MAY2011			TE Connectivity	
CHK	17MAY2011				
APVD	17MAY2011				
PRODUCT SPEC	108-19460				
APPLICATION SPEC		NAME SPLASH-PROOF MICRO USB B-TYPE 0,8 mm OFFSET			
-					
WEIGHT 0,33					
		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
		A3	00779	Ⓒ-2173157	-
Customer Drawing			SCALE 8:1	SHEET 1 OF 3	REV A1

THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ±0,2 1 PLC ±0,1 2 PLC ±0,1 3 PLC ±0,025 4 PLC ±0,001 ANGLES ±2°
MATERIAL	FINISH
-	-

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD



-

SEE SHEET 1


-

-



-



SECTION B - B



REEL DIA 330




SECTION C - C

NOTES:
COVER, EMBOSS TAPE AND REEL ACCODING EIA STANDARD 481-D

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm



MATERIAL

-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±0,2
1 PLC ±0,1
2 PLC ±0,1
3 PLC ±0,025
4 PLC ±0,001
ANGLES ±2°

FINISH

-

DWN 17MAY2011

W. Jansen

CHK 17MAY2011

W. Jansen

APVD 17MAY2011

D. Halberstadt

PRODUCT SPEC

108-19460

APPLICATION SPEC

-

WEIGHT

0,33

Customer Drawing



TE Connectivity

NAME

SPLASH-PROOF MICRO USB
B-TYPE
0,8 mm OFFSET

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-2173157

-

SCALE

8:1

SHEET

2

OF

3

REV

A1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION


DATE

DWN


APVD

SEE SHEET 1

SEE DETAIL B




SECTION D-D



COVER RIB



PWB

DETAIL B
SCALE 6:1



SCALE 2:1


SEE DETAIL A



RECOMMENDED COVER HOLE SHAPE (REF)

DETAIL A
SCALE 8:1

0,3±0,2




3,75±0,05
HEIGHT FROM PWB TO
RIB COVER

3,1 REF

SECTION A-A

RECOMMENDED PWB AND COVER ASSEMBLY (REF)




15,00 REF

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm



TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±0,2
1 PLC ±0,1
2 PLC ±0,1
3 PLC ±0,025
4 PLC ±0,001
ANGLES ±2°

MATERIAL

-

FINISH

-

DWN 17MAY2011

W. Jansen

CHK 17MAY2011

W. Jansen

APVD 17MAY2011

D. Halberstadt

PRODUCT SPEC

108-19460

APPLICATION SPEC

-

WEIGHT

0,33

Customer Drawing



TE Connectivity

NAME

SPLASH-PROOF MICRO USB
B-TYPE
0,8 mm OFFSET

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-2173157

-

SCALE 8:1

SHEET 3 OF 3

REV A1