







REVISIONS				
P	LTR	DESCRIPTION	DATE	DWN APVD
	2	REVISED PER ECR-17-015922	06NOV2017	BDA KR



- MATES WITH APPROPRIATE UNIVERSAL MATE-N-LOK™ PLUG.
 - DIMENSIONS SHOWN REPRESENT PRODUCT IN DRY, AS MOLDED, CONDITION. ADDITIONAL 2% GROWTH DUE TO SUBSEQUENT MOISTURE ABSORPTION MAY OCCUR AND SHOULD BE ACCOUNTED FOR
- 3 FOUR RIBS EQUALLY SPACED, NO SPECIFIC ORIENTATION. NO RIBS OR SIX RIBS EQUALLY SPACED, NO SPECIFIC ORIENTATION, OPTIONAL.
- 4 PRELIMINARY- NOT FOR PRODUCTION.




DETAIL A
OPTIONAL CONSTRUCTIONS



3-DIMENSIONAL MODEL
NTS

27.43	1.080
19.05	.750
13.97	.550
7.62	.300
0.38	.015
0.13	.005
MM	IN
CONVERSION TABLE	

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN ASHWINI.V	27JAN2014	NATURAL		2178927-1													
				CHK GK	27JAN2014	COLOR		PART NO													
				APVD KD	27JAN2014	STE		TE Connectivity													
DIMENSIONS:		TOL. FRANCES, UNLESS OTHERWISE SPECIFIED:		NAME		CAP,2 CIRCUIT UNIVERSAL MATE-N-LOK															
mm																					
		0	PLC	±	—	SIZE															
		1	PLC	±	—					CAGE CODE											
		2	PLC	±	—									DRAWING NO							
		3	PLC	±	0.13													RESTRICTED TO			
		4	PLC	±	—																
ANGLES		±	1°	CUSTOMER DRAWING																	
FINISH		—						SCALE													
MATERIAL		NYLON,UL 94V-0										4:1									
																SHEET					
																				1 OF	
				REV																	
								2													