









LEVER OPERATION SIDE
Hebel Betaetigungsseite




1- -1 AS SHOWN
wie gezeichnet

LEVER OPERATION SIDE
Hebel Betaetigungsseite





1- -2 AS SHOWN
wie gezeichnet

CODINGS/Codierung




POS	DESCRIPTION
1	3POS, 8mm HV, REC HSG, 180°, ASSY, SEALED 3pol, gedichtete Assy, 8mm HV, 180°




2208669-3	16	9.65	9.65±0.97	5.85±0.10
2208669-3	25			6.50±0.10
2208608-3	35	11.70	11.70±1.17	7.50±0.15
2208608-3	50			8.45±0.15
TE-ORDER-NO.	Wire Size	Cb1 (mm)	Cb1m (mm)	Ch1 (mm)
TE-Bestell-Nr.	(mm2)			


POS	DESCRIPTION
2	HV 8mm Socket Terminal, 180° HV 8mm Buchsenkontakt, 180°





POS	DESCRIPTION
3	SHIELDING SLEEVE, 180° Schirmhülse, 180°






POS	DESCRIPTION
4	FINGER PROT CAP 8mm HV, 180° Fingerschutzkappe 8mm HV, 180°



POS	DESCRIPTION
5	INSULATION INSERT, 180° Isolationskörper, 180°






POS	DESCRIPTION	TE-ORDER-NO.
6	SHIELD CRIMP FERRULE, INNER Unterfercrimphülse	2177061-1 Alternative 2177061-2





2177090-3	12.5
2177090-2	14.8
2177090-1	16.2
TE-ORDER-NO.	DIMENSION A
TE-Bestell-Nr.	Mass A




POS	DESCRIPTION
7	SHIELD CRIMP SLEEVE Schirm, Crimpbuchse





2141156-4	8.0
2141156-3	10.6
2141156-2	12.5
2141156-1	13.6
TE-ORDER-NO.	DIMENSION A
TE-Bestell-Nr.	Mass A



POS	DESCRIPTION
8	SINGLE WIRE SEAL, 8mm HV, 90° Kabeldichtung einzeln, 8mm HV, 90°



2141155-4	10.6
2141155-3	12.6
2141155-2	14.8
2141155-1	16.2
TE-ORDER-NO.	DIMENSION A
TE-Bestell-Nr.	Mass A



POS	DESCRIPTION
9	PROTEC. COVER 8mm HV, 90° Abdeckkappe 8mm HV, 90°



TOLERANCING ISO 8015 TOLERIERUNG ISO 8015										DIESE ZEICHNUNG IST EIN KONTROLLIERTES DOKUMENT. BESAMMUNGEN UND TOLERANZEN GEMÄSS: GPS ISO STANDARDS.										DATE: 21NOV2014 DRAWN: J. Tabolati CHECKED: J. H. Vu APPROVED: J. Tabolati PRODUCT SPEC: 21NOV2014 APPLICATION SPEC: 21NOV2014										MATERIAL: SEE TABLE FINISHING: SEE TABLE CUSTOMER DRAWING										SCALE: 1:1 SHEET: 2 REV: C									
TOLERANCING ISO 8015 TOLERIERUNG ISO 8015										DIESE ZEICHNUNG IST EIN KONTROLLIERTES DOKUMENT. BESAMMUNGEN UND TOLERANZEN GEMÄSS: GPS ISO STANDARDS.										DATE: 21NOV2014 DRAWN: J. Tabolati CHECKED: J. H. Vu APPROVED: J. Tabolati PRODUCT SPEC: 21NOV2014 APPLICATION SPEC: 21NOV2014										MATERIAL: SEE TABLE FINISHING: SEE TABLE CUSTOMER DRAWING										SCALE: 1:1 SHEET: 2 REV: C									

TE Connectivity

3POS 8mm HV KIT, 180DEG, SEALED
3pol 8mm HV Kit, 180Grad, gedichtet
OVERVIEW / Uebersicht, ASSY

SIZE: 100779 C=2177062

INSTRUCTIONS: SEE TABLE

[illegible]

NOTE Bem.	FEATURE Merkmal
4	PRODUCT-SPEC. 108-94297 Produkt-Spez.
5	APPLICATION SPEC. 114-94130 Verarbeitungsspez.

A

4826 13/13