







LOC	DST	REVISIONS				
		#	REV	DESCRIPTION	DATE	DM
GA	1	A		INITIAL REL. PER LC20-0067-13	11JUN2013	DM
		B		LC20-0112-13 / ECO-13-017535	04NOV2013	DM
		C		LC20-0125-13 / ECO-13-018512	20NOV2013	DM



WEDGE MARKING FOR ASSEMBLY 2182246-1



WEDGE MARKING FOR ASSEMBLY 2182246-2



WEDGE MARKING FOR ASSEMBLY 2182246-3

- 1 WIRE SIZES CORRESPONDING TO PART NUMBERS ARE MARKED ON WEDGE IN RED COLOR ACCORDING TO ORIENTATIONS SHOWN.
- 2 INHIBITOR IS APPLIED AT FACTORY TO GROOVES OF WEDGE AND C BODY.
3. DIMENSIONS ARE FOR REFERENCE ONLY.
4. USE RED SHELL NO. 69338-2.

4 Cu Str, 6 3SS, 4 ACSR 2 Str, 4A CW	2 Str, 4A CW	2182246-3
4 CU Str, 6 3SS, 4 ACSR	4 Cu Str, 6 3SS, 4 ACSR	2182246-2
6 CU Sol, 8A CW, 4 CU Sol	4 Cu Str, 6 3SS, 4 ACSR 2 Str, 4A CW	2182246-1
TAP	RUN	PART NO.
CONDUCTOR RANGE 		

2	A/R	A/R	A/R	INHIBITOR	3
1	-	-	-	WEDGE, ALUM	2
-	1	-	-	BODY, ALUM	1
-3	-2	-1	-	DESCRIPTION	ITEM NO
QTY PER ASSY				PARTS LIST	

THIS DRAWING IS A CONTROLLED DOCUMENT. DWG: D. MURUGIAH 11JUN2013
CHK: B. JOHNSON 21JUN2013
APPD: B. JOHNSON 21JUN2013

DIMENSIONS: INCHES
TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±
1 PLC ±
2 PLC ±.03
3 PLC ±.005
4 PLC ±.005
ANGLES ± 0° 30'

MATERIAL SEE BOM FINISH NONE

TE Connectivity
TAP CONNECTOR, SPECIAL, RED CODED, AMPACT

APPLIC. SPEC: -
WEIGHT: -
CUSTOMER DRAWING

SIZE: A2
CAGE CODE: 00779
DRAWING NO: C=2182246
RESTRICTED TO: -
SCALE: NTS
SHEET: 1 of 1
REV: C