

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT -

ALL RIGHTS RESERVED.

3

54.2±0.05

1±0.13

SEE DETAIL F

60

A

35.75

40.5

48.2

56.2

62.5

SCALE 3:2

8.6 REF

4.8

11.15

4.1

0.2

2.95 TYP

DETAIL F

SCALE 4:1

NORMALY CLOSED

SCALE 4:1

NORMALY OPEN

SCALE 4:1

LOC

DIST

IR

-

P

LTR

A

DESCRIPTION

ECR-13-008316

DATE

21MAY2013

DWN

GG

APVD

RRP

NOTES:

CONTACTS PLATING :

1

OVERALL: Ni 2µm MIN,ALL OVER THE CONTACTS.
SOLDER ZONE: Sn 2.5µm MIN ON THE SOLDER ZONE OF THE CONTACTS.
MATING ZONE: GOLD FLASH

2

OVERALL: Ni 2µm MIN,ALL OVER THE CONTACTS.
SOLDER ZONE: Sn 2.5µm MIN ON THE SOLDER ZONE OF THE CONTACTS.
MATING ZONE: PdNi WITH GOLD

3

MATERIAL :

HOUSING: PBT-GF, BLACK UL 94V0.
CONTACTS: COPPER ALLOY.

4

TE SMART CARD RECEPTACLE DESIGNED TO ACCEPT ISO 7810-7816 TYPE
INTEGRATED CIRCUIT SMART CARDS (0.76MM REF. THICKNESS) SEE SHEET 2/2

5

LOGO SHAPE AND POSITION VARY DEPENDING ON
MOLD CAVITY NUMBER.

6

DIMENSION APPLICABLE IN CARD CONTACT AREA ONLY
SURFACE VARY DEPENDING ON MOLD CAVITY NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± 0,5
1 PLC ± 0,3
2 PLC ± 0,03
3 PLC ± 0,001
4 PLC ± 0,0001
ANGLES ± -
FINISH

MATERIAL

3

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

GUNA

GUNA

RAJENDRA

108-64029

9 g

-

20DEC2012

20DEC2012

20DEC2012

108-64029

9 g

-

NAME

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

TE Connectivity

A2

C-2178428

-

SMART CARD READER 0.76mm,PCB
MOUNT THROUGH HOLE, HIGH PROFILE
SWITCH NORMALLY OPEN AND CLOSE

SCALE 1:1

SHEET 1 OF 2

REV A

1471-9 (3/11)

