



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	PRODUCTION RELEASE	23AUG2019	ES	SH
	A1	REVISED PER ECN-22-166164	26JUL2022	IT	SZ
	A2	REVISED PER ECN-24-252036	20MAR2024	AP	RS



- ⚠ MATERIAL:
CAGE ASSEMBLY - 0.25mm THICK NICKEL SILVER ALLOY.
GASKET RETENTION PLATE: STAINLESS STEEL.
EMI GASKET - PLATED FILLED SILICONE.
PCB GASKET - RF ABSORBER.
2. MINIMUM PC BOARD THICKNESS:
SINGLE SIDED = 1.50mm
3. MATES WITH SFP MSA COMPLIANT TRANSCEIVERS.
- ⚠ PADS AND VIAS CHASSIS GROUND.
- ⚠ DATUM AND BASIC DIMENSION ESTABLISHED BY CUSTOMER.
- ⚠ REFERENCE APPLICATION SPEC. 114-13120, HOLE A, FOR
RECOMMENDED DRILL HOLE DIAMETER AND PLATING THICKNESS.
- ⚠ REFERENCE APPLICATION SPEC. 114-13120, HOLE B, FOR
RECOMMENDED DRILL HOLE DIAMETER AND PLATING THICKNESS.
- ⚠ REFERENCE APPLICATION SPEC. 114-13120, HOLE C, FOR
RECOMMENDED DRILL HOLE DIAMETER AND PLATING THICKNESS.
- ⚠ CONTACT STANDOFF WILL PIERCE GASKET WHEN PROPERLY PRESSED INTO PCB.



STANDARD TYPE	2198709-1	1
DESCRIPTION	PART NO	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN LEO LI 14SEP2016	TE TE Connectivity	
DIMENSIONS:		CHK SEAN HAN 14SEP2016		
mm		APVD SEAN HAN 14SEP2016		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC		
0 PLC ±0.1		108-2364	NAME ZSFP+ 1X1 CAGE ASSEMBLY, PRESS-FIT STANDARD, EMI GASKET	
1 PLC ±0.1		APPLICATION SPEC		
2 PLC ±0.1		114-13120	SIZE A1	
3 PLC ±0.05		WEIGHT		
4 PLC ±0.05		CUSTOMER DRAWING	SCALE 5:1	
ANGLES ±0.05				
FINISH			SHEET 1 OF 2	
MATERIAL				
⚠			REV A2	

