






2		1					
LOC	DIST	REVISIONS					
DS	-	P	LTR	DESCRIPTION	DATE	DWN	APVD
			B	REVISED (ECR-15-000140)	06/JAN/15	WY	HG
			C	REVISED (ECR-19-004821)	15APR2019	CH	YJ
			C I	REVISED (ECR-24-222142)	27SEP2024	SW	YH

KEY-CODE

2188289-2 (A)
APPLIED PLUG ASSY: 2005372-2

2-2188289-3 (B)
APPLIED PLUG ASSY: 2005372-3/4




NOTE
1. GENERAL TOLERANCE: ± 0.3 , 3°
2. CONDITION OF DELIVERY: 1ST, LOCKING CONDITION WITH DBL PLATE OPEN POSITION.
3. APPLICABLE RECEPTACLE CONTACT P/N: BELOW TABLE

CONTACT	MT-11
PART NO.	963902-1, 963904-1, 1703278
WIRE SIZE(mm2)	c1 0.3 ~ 0.5 / >0.5 ~1.0 / 1.25
WIRE SEAL PART NO.	964971-1, 963530-1, 964972-1, 2219708-4

2	NATURAL	PA66-GF35	DBL HSG	I	I
	GRAY	PA66-GF35	CAP HSG-B	I	-
I	BLACK	PA66-GF15	CAP HSG-A	-	I
	NO	COLOR	MATERIAL	DESCRIPTION	Q'TY

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm



MATERIAL SEE TABLE

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	$\pm$
1 PLC	$\pm$
2 PLC	$\pm$
3 PLC	$\pm$
4 PLC	$\pm$
ANGLES	$\pm$
FINISH	$\pm$

DWN
WY JANG

CHK
KT LIM

APVD
HG CHO

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

Customer Drawing



TE Connectivity

NAME
MT-11 SLD 6P CAP ASSY

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-2188289	-

SCALE	SHEET	OF	REV
1:1	1	1	C1