



REVISIONS					
P	LYR	DESCRIPTION	DATE	DWN	APVD
B5		REVISED (ECN-25-307140)	19FEB2025	JS	YH
B4		REVISED (ECR-24-216040)	24JUL2024	JS	YH
B3		REVISED (ECR-24-210760)	05JUL2024	JS	YH
B2		REVISED (ECR-23-163814)	16JAN2023	SY	KT




Terminal P/N	Circuit Number
2188339-6(TIN)	4-6
2188339-9(GOLD)	1-3
2188339-4(TIN)	9-12
2188339-8(GOLD)	7,8
2188339-2(TIN)	13-18







3D VIEW

TYPE 1 1-2188336-2 / 2188336-2	TYPE 2 1-2188336-4	TYPE 3 2-2188336-4	B5 TYPE 4 3-2188336-7

SCALE 1:1



SECTION A-A




SECTION B-B
SCALE 2:1

- NOTE
1. GENERAL TOLERANCE : ± 0.3 , $\pm 3^\circ$
 2. APPLICABLE COUNTER PART (PLUG) P/N : 1897688-X
 3. MAX WARPAGE : 0.3mm
 4. 1-2188336-4 COLOR RAL CODE : RAL 1011
 5. TAB TIN PLATING : TYPE A Sn (MATTE), (MS915-01)

NO	P/N	DESCRIPTION	MATERIAL	COLOR	Q'TY
9	1-2188338-2	JOINT HSG	PA66-GF15	BLACK	-
8	2188338-1	JOINT HSG	PA66-GF15	NATURAL	1
7	2188339-9	1.5MM TAB(L)	BRASS	GOLD	3
6	2188339-6	1.5MM TAB(L)	BRASS	TIN	3
5	2188339-8	1.5MM TAB(M)	BRASS	GOLD	2
4	2188339-4	1.5MM TAB(M)	BRASS	TIN	4
3	2188339-7	1.5MM TAB(S)	BRASS	GOLD	-
2	2188339-2	1.5MM TAB(S)	BRASS	TIN	6
B5	3-2188337-7	HEADER HSG	PA66-GF30	GREEN	-
1	2-2188337-4	HEADER HSG	PA66-GF30	BROWN	-
	1-2188337-4	HEADER HSG	PA66-GF30	BROWN	-
	2188337-2	HEADER HSG	PA66-GF30	BLACK	1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DGS JEONG			NAME 060 18P HDR ASSY	
DIMENSIONS: mm		CHK KT LIM				
		APVD HG CHO	PRODUCT SPEC		SIZE A	
		PRODUCT SPEC	APPLICATION SPEC		CAGE CODE 00779	
MATERIAL -		WEIGHT -	CUSTOMER DRAWING		SCALE 1:1	
					SHEET 1	
					OF 1	
					REV B5	

FIG 1. PRINTED PCB LAYOUT



1. GENERAL TOLERANCE : ± 0.1
2. APPLICABLE P.C.B THICKNESS : 1.6 mm