

8 THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	7 20		6	
C COPYRIGHT 20 (5.20) (5.20) (5.20) KEY CODE SCALE 4:		(3.40) (3.40) (CODE KEY CODE SCALE 4:		(0.60)	
<ul> <li>2. TERMINALS SOLE WIRE SEAL, SEE</li> <li>3. APPLICABLE INT</li> <li>A MINIMUM FEED-T</li> <li>5. TRACEABILITY C S = 1 DIGIT SE</li> <li>6. FOR OPTIONAL T CUSTOMER SERVI</li> <li>6. FOR OPTIONAL T CUSTOMER SERVI</li> <li>5. SEE INSTRUCTIC ISL ACTUATION</li> <li>8. PRIMARY LOCK T</li> <li>SEE INSTRUCTIC ISL ACTUATION</li> <li>8. PRIMARY LOCK T</li> <li>ACTUATION</li> <li>ACTUATION&lt;</li></ul>	2 SEPARATELY. F TABLE TERFACE DRAWING THROUGH CONDITI CODE (YY = TWO HIFT). TERMINAL CAVITY ICE ON SHEET 408-32 DISTANCE IS 2. TERMINAL RETENT IG AND APPLICAB ES REPRESENTAT DETAILS, SEE C.D. IS SPECIFI HLY DEPENDENT CON TERMINAL SEE C.D. IS SPECIFI HLY DEPENDENT CON SONTACT INSERTIC ONTACT INSERTIC	FION FORCE 25N MIN BLE INDIVIDUAL WIRE FIVE OR CUSTOMER SI TE APPLICATION SPE ED TO MEET MOST WI DN INSULATION TYPE	ON 1.2mm CLEA 03-1-Z01 AND ARANCE ALL AR 3 DIGIT JULI T TE SALES RE SERVICE AND IMUM. E SEAL ARE AP ERVICE FOR DE ECIFICATION 1 IRE SEAL APPL AND O.D. SUF L DOES NOT DI HOUSING. THE RS DURING THE RS DURING THE	N BODY CONTACT 120-2-003-1-Z02 OUND AN DAY, PRESENTATIVE OR ISL OPERATION, PLICATION DEPENI TAILS 14-18464. ICATIONS. HOWEY FICIENT GRIP OF SPLACE FROM INS WIRE SEAL SHAL CRIMPING OPERA TION. FOR DIMENS	DENT, VER, THE ULATION L NOT TION.
- WIRE	CRIMP NSIONS	INSULATION         DIMENSI			125°С

4805 (3/13)

 $T \in MP \xrightarrow{9}$ 




5




3

4



ISL SHOWN IN FINAL POSITION REF ONLY




ISL SHOWN IN Pre-latched position


								BLACK	D	2203806-4
								DK GRAY	С	2203806-3
								LT GRAY	В	2203806-2
								BLACK	A	2203806-1
								ISL COLOR	KEY CONFIGURATION	P A R T N U M B E R
						THIS DRAWING IS A	CONTROLLED DOCUMEN	Т. <u>Dwn</u> 25MAY2011 <u>M. HARISH</u> снк 25MAY2011 В. BUCHTER	-ETE	TE Connectivity
1418844	1.40 - 1.90mm				967067-1	DIMENSIONS: MM	TOLERANCES UNLESS OTHERWISE SPECIFIED	B. BUCHTER	NAME PLUG AS	SEMBLY,
1670146	1.40 - 1.90mm		10		967067-1		0 PLC ±- 1 PLC ±- 2 PLC ±-	PRODUCT SPEC	FEMALE, SEALEI	D, 3 PÓSITION, I SIR
1418850	1.90 - 2.40mm				964972-1		∫ 3 PLC ±- 4 PLC ±-	APPLICATION SPEC	SIZE CAGE CODE DRAWING NO	RESTRICTED TO
FEMALE	APPLICABLE WIRE			ICD	WIRE SEAL 🔨		ANGLES ±- FINISH		-A100779 C-2203806	-
TERMINAL P/N	FINISHED O.D.	W.C.H	W.C.W	I.C.D	PART NUMBER 🖉	·	-	CUSTOMER DRAWING	SCALE	5:1 SHEET OF REV C

	REVISIONS			
LTR	DESCRIPTION	DATE	DWN	APVD
В	REVISED PER ECO-17-001086	25JAN2017	DD	JT
С	REVISED PER ECO-17-003504	14MAR2017	DLD	JLT

1



ISOMETRIC VIEW SCALE 4:1



В