

D

D

C

C

B

B

A

A




TABLE 1.


CONTACT	PART NO.	WIRE SIZE(SQ)
.025 TH	2005097-1	0.13~0.22
	2005427-1	0.3~0.5
.060	2109006-1	0.22~0.35
	2109006-2	0.5~0.75
	2109006-3	0.85~1.25
.110 (MCP2.8)	1-968880-1	0.35~0.5
	1-968849-1	>0.5~1.0
	1-968851-1	>1.0~2.5
	1-968853-1	>2.5~3.0
.250 (MCP6.3)	1241402-1	0.5~1.0
	1241404-1	>1.0~2.5
	1241406-1	>2.5~4.0
	1241408-1	>4.0~6.0

- NOTE
- 1. GENERAL TOLERANCE: ± 0.3 , $\pm 3^\circ$
 - 2. CONDITION OF DELIVERY: DBL IN 1st LOCKING POSITION, LEVER IN 2nd LOCKING POSITION
 - 3. APPLICABLE RECEPTACLE CONTACT P/N: <TABLE1>
 - 4. APPLICATION INTERFACE P/N: 114-61062

HYB 38P PLUG ASSY-A FOR AD	HYB 38P PLUG ASSY-A	HYB 38P PLUG ASSY-B	HYB 38P PLUG ASSY-A	HYB 38P PLUG ASSY-C	DESCRIPTION
2-2188532-2	2188532-2	1-2188532-1	2188532-8	2188532-3	ASSY P/N

4	BLACK	POM	HYB 38P LEVER HSG FOR AD	1	-	-	-	-
	GRAY		HYB 38P LEVER HSG	-	1	1	1	1
2	NATURAL	PBT	HYB 38P DBL HSG-A	2	2	-	2	2
	BLACK		HYB 38P DBL HSG-B	-	-	2	-	-
1	B2 GRAY	PBT	HYB 38P PLUG HSG-C	-	-	-	-	1
	BLUE		HYB 38P PLUG HSG-A	-	-	-	1	-
	NATURAL		HYB 38P PLUG HSG-B	-	-	1	-	-
	BLACK		HYB 38P PLUG HSG-A	1	1	-	-	-
NO	COLOR	MATERIAL	DESCRIPTION	Q'TY				

KEY-CODE		
2188532-2/8 (A)	1-2188532-1 (B)	2188532-3 (C) B2



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±
FINISH

MATERIAL

SEE TABLE

DWN WY JANG
CHK YH MA
APVD KT LIM
PRODUCT SPEC 108-61227
APPLICATION SPEC -
WEIGHT 32.7

Customer Drawing

TE Connectivity

025/ 060/ 110/ 250 LIF 38P PLUG ASSY

SIZE A2 CAGE CODE 00779 DRAWING NO C-2188532 RESTRICTED TO -

SCALE 1:1 SHEET 1 OF 1 REV B2