






LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-		C	REVISED(ECR-23-164988)	12AUG2024	DG	YH



REFERENCE PCB LAY-OUT for 2188692-1
*P.C.B THICKNESS : 1.6 ± 0.05 mm

C	9	TIN PLATED	COPPER ALLOY	.020 TAB SHORT	19	19	19	
	8	TIN PLATED	COPPER ALLOY	.020 TAB MIDDLE	19	19	19	
	7	TIN PLATED	COPPER ALLOY	.020 TAB LONG	19	19	19	
	6	TIN PLATED	COPPER ALLOY	.060 TAB SHORT SHORT	4	4	4	
	5	TIN PLATED	COPPER ALLOY	.060 TAB SHORT	4	4	4	
	4	TIN PLATED	COPPER ALLOY	.060 TAB MIDDLE	4	4	4	
	3	TIN PLATED	COPPER ALLOY	.060 TAB LONG	4	4	4	
	11	BLACK	PA46-GF15	JOINT PLATE TYPE C	1	-	-	
	10	GRAY		JOINT PLATE TYPE B	-	1	-	
	2	BLACK		JOINT PLATE	-	-	1	
12	NATURAL	LCP-GF30	020/060 73P HEADER HSG TYPE C	1	-	-		
NO		LCP-GF30	020/060 73P HEADER HSG	-	1	1		
	NO	COLOR	MATERIAL	DESCRIPTION			QT'Y	

- NOTE
1. GENERAL TOLRANCE: ± 0.3 , $\pm 2.0^\circ$
 2. THE MATING PLUG ASS'Y P/N: 2188698, 2188701
 3. SEE TO SHEET 1 : 2188692-1
 4. SEE TO SHEET 2 : 1-2188692-1, 3-2188692-1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DG JEONG		 TE Connectivity	
		CHK			
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME 020/060 73P HEADER ASSY	
mm		APVD KT LIM			
		PRODUCT SPEC 108-61226			
		APPLICATION SPEC -			
MATERIAL		FINISH		SIZE	RESTRICTED TO
-		-		A2	-
				DRAWING NO	
				C-2188692	
				SCALE	
				SHEET	
				OF	
				REV	

