









REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASED PER ECO-16-009783	30JUN2016	DD	MB







- NOTE(S):
- 1. MATERIAL: PA66, 10% GLASS FILLED, NATURAL (BROWN)
  - 2. KEYING OPTION "A" SHOWN IN GENERAL VIEWS.
  - 3. APPLICABLE TERMINALS: MCON 1.2 LOCKING LANCE TERMINAL PN 1452656 IN ALL CAVITIES  
PN 1452659 IN CAVITIY 7 AND 14.
  - 4. DATE CODE INDICATOR IN THIS APPROXIMATE AREA.
  - 5. TE PART NUMBER TO BE SHOWN IN THIS APPROXIMATE AREA.
  - 6. MATERIAL ID SHOWN IN APPROXIMATE AREA.
  - 7. IF PRODUCT IS RECEIVED WITH SECONDARY LOCKS IN CLOSED POSITION, INSERT TIP OF SMALL SCREWDRIVER IN THIS LOCATION TO PRY LOCK OPEN.

SCALE 4:1	SCALE 4:1	SCALE 4:1	SCALE 4:1
KEYING OPTION "A"	KEYING OPTION "B"	KEYING OPTION "C"	KEYING OPTION "D"



D	2203464-4
C	2203464-3
B	2203464-2
A	2203464-1
KEYING OPTION	TE PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. HITCHCOCK 29AUG2012	 TE Connectivity	
DIMENSIONS:		CHK H. BECK 29AUG2012		
mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:	NAME	
			UNSEALED PLUG, 14 POSITION 1-PIECE MCON	
	MATERIAL	FINISH	SIZE CAGE CODE DRAWING NO	
			A100779C=2203464	
			RESTRICTED TO	
			-	
CUSTOMER DRAWING			SCALE 6:1	SHEET 1 OF 1 REV A