







LOC		DIST		REVISIONS						
P	LTR	DESCRIPTION			DATE	DWN	APVD			
B		REVISED PER ECO 13-001843.			08FEB2013	MGM	CT			



SINGLE POLARIZATION



DOUBLE POLARIZATION



CAVITY IDENTIFICATION WHEN VIEWED FROM MATING FACE CONNECTOR

1 THE PART IS MARKED WITH THE TE PART NUMBER, CHINA, DATE CODE AND LOT ID.

2. DWV RATING: 725VAC @ SEA LEVEL
3. WIRE SIZE: 28 AWG MAX
4. WORKING TEMPERATURE: -55°C ~ +125°C

5 MATERIAL:

CONTACT : COPPER ALLOY

SHELL : COPPER ALLOY

INSULATOR : PEEK

6 FINISH

CONTACT: GOLD OVER NICKEL

SHELL : BLACK CHROMIUM

7 ALL TOLERANCES ±0.20MM UNLESS NOTED.

CHROMIUM-BLACK	DOUBLE	SOLDER CUP	10	11	33.35	ø12.5	ø15.5	3	2221365-2
CHROMIUM-BLACK	SINGLE	SOLDER CUP	10	11	33.35	ø12.5	ø15.5	3	2221365-1
FINISH	POLARIZATION	TERMINATION	Q	S	L	d	D	SHELL SIZE	TE PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN	05JUL12	TE Connectivity			
				CHK	05JUL12				
				APVD	05JUL12	NAME			
				PRODUCT SPEC					
				APPLICATION SPEC		CIRCUULAR HD PLUG WITH SOCKET CONTACTS 19 POS. SHELL S/Z 1031			
				WEIGHT	-	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
						A2	00779	C=2221365	-
				CUSTOMER DRAWING				SCALE	SHEET
								NTS	1 of 1
									REV B