







LOC		DIST		REVISIONS						
-		-								
		P	LTR	DESCRIPTION			DATE	DWN	APVD	
			-	SEE SHEET 1			-	-	-	



THE DISTANCE IS 0.05 MM MATING FACE FROM R/A PLUG TO VERTICAL REC.



THE DISTANCE IS 1.4 MM MATING FACE FROM R/A PLUG TO VERTICAL REC.
2204443-1/1-2204423-5




PART NUMBER	POWER			
	M4	M3	M2	M1
2204423-5	MM	MM	MN	MN
4MP				


POWER CONTACT MFBL UNMATING 1.4MM	PA
POWER CONTACT STANDARD UNMATING 1.4MM	PB
MIDDLE POWER CONTACT MFBL	MM
MIDDLE POWER CONTACT STANDARD	MN
POWER CONTACT MFBL	PM
POWER CONTACT STANDARD	PN
DESCRIPTION	CODE

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN THOMAS_ZHAO 28JUN2013	 TE Connectivity			
		CHK SUNY_ZHAO 28JUN2013				
DIMENSIONS:		APVD SUNY_ZHAO 28JUN2013	NAME	Customer Drawing VERTICAL RECEPTACLE PRESS FIT MUTIL-BEAM HD W/GUIDELESS	RESTRICTED TO	
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	PRODUCT SPEC				
	0 PLC ±0.4	APPLICATION SPEC	SIZE	CAGE CODE	DRAWING NO	
	1 PLC ±0.4					
	2 PLC ±0.25					
	3 PLC ±0.15					
	4 PLC ±					
	ANGLES ±	WEIGHT	A1	-	C=2204423	
	FINISH					
MATERIAL		CUSTOMER DRAWING	SCALE	8:1	SHEET 2 OF 6	REV A9


LOC		DIST		REVISIONS			
P	LYR	DESCRIPTION		DATE	DWN	APVD	
-	-	SEE SHEET 1		-	-	-	




PCB LAYOUT PART NUMBER: 2204423-2




PCB LAYOUT PART NUMBER:
2204423-3/1-2204423-1




PCB LAYOUT PART NUMBER: 2204423-4



PCB LAYOUT PART NUMBER: 2204423-8



PART NUMBER: 2204423-2



PART NUMBER	POWER	
	P2	P1
2204423-2	PM	PN
2P		



PART NUMBER	POWER			
	P4	P3	P2	P1
2204423-3	PM	PM	PM	PM
4P				

PART NUMBER	POWER					
	P6	P5	P4	P3	P2	P1
2204423-4	PM	PM	PM	PM	PM	PM
6P						



PART NUMBER	POWER			
	P4	P3	P2	P1
2204423-8	PM	PM	PM	PM
4HVP				

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN THOMAS ZHAO 28JUN2013	TE Connectivity	
		CHK SUNY ZHAO 28JUN2013		
DIMENSIONS:		APVD SUNY ZHAO 28JUN2013	NAME Customer Drawing VERTICAL RECEPTACLE PRESS FIT MULTI-BEAM HD W/GUIDELESS	
mm		PRODUCT SPEC		
		APPLICATION SPEC	SIZE A1	
		WEIGHT		
MATERIAL		CAGE CODE	DRAWING NO. C=2204423	
		FINISH		
		RESTRICTED TO	SCALE 8:1	
		REV A9		
		SHEET 3 OF 6		

LOC		DIST		REVISONS			
P	LTR	DESCRIPTION		DATE	DWN	APVD	
-	-	SEE SHEET 1		-	-	-	







PART NUMBER	POWER	
	LP2	LPI
2204423-6	LM1	LM1
	LM2	LM2
4LP		





LP TOP CONTACT MFBL PRESS FIT	LM1
LP BOTTOM CONTACT MFBL PRESS FIT	LM2
DESCRIPTION	IDENTIFIER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN THOMAS_ZHAO 28JUN2013	TE Connectivity	
		CHK SUNY_ZHAO 28JUN2013		
DIMENSIONS:		APVD SUNY_ZHAO 28JUN2013	NAME	
mm		PRODUCT SPEC	Customer Drawing	
		APPLICATION SPEC	VERTICAL RECEPTACLE PRESS FIT	
		WEIGHT	MUTIL-BEAM HD W/GUIDELESS	
MATERIAL		SIZE	CAGE CODE	DRAWING NO
		A1	-	©=2204423
		CUSTOMER DRAWING		RESTRICTED TO
		SCALE 8:1		SHEET 4 OF 6
				REV A9



PART NUMBER: 1-2204423-1
PCB LAYOUT REFER: 2204423-3



PART NUMBER	POWER							
	P8	P7	P6	P5	P4	P3	P2	P1
1-2204423-3								
8P								

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 28JUN2013 THOMAS ZHAO CHR 28JUN2013 SUNDY ZHAO APVD 28JUN2013 SUNDY ZHAO		 TE Connectivity			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ±0.4 2 PLC ±0.25 3 PLC ±0.15 4 PLC ± ANGLES ±° ±°		NAME Customer Drawing VERTICAL RECEPTACLE PRESS FIT MUTIL-BEAM HD W/GUIDELESS			
		PRODUCT SPEC - APPLICATION SPEC -		SIZE A 1		CAGE CODE -	
MATERIAL 		FINISH 		DRAWING NO C=2204423		RESTRICTED TO -	
CUSTOMER DRAWING				SCALE 8:1		SHEET 6 OF 6	
				REV A 9			