




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	C3	REVISED PER ECR-25-238462	25MAR2025	CJH	TD

- 1
- CONTINUOUS STRIP ON REELS WITH TERMINALS LOCATED ON 8.38±0.076[.330±.003] CENTERS
- 2
- SLOT ACCEPTS DETAILS SEE CHART
- 3
- REFER TO DWG 87-1039-3 FOR ADDITIONAL CAVITY INFORMATION (MODIFIED DEPTH)
- 4
- 0.0010 [.000040] MIN TIN PLATE
- 5
- 0.45mm SINGLE AL WIRE AND 0.36-0.51mm SINGLE AND DOUBLE COPPER WIRE HAS TO BE QUALIFIED -TBD
- 6
- WIRE DIAMETER TOLERANCE ALLOW ±0.005mm
- 7
- NUMBER 10 FOR 2232555-1;NUMBER 9 FOR 2232555-3

4	0.45-0.51	0.36-0.51	0.50-0.51	0.36-0.51	PAPER	2232555-3 5						
4	0.51-0.64	0.36-0.57	0.51-0.64	0.36-0.57	PAPER	2232555-1						
FINISH	Al WIRE	Cu WIRE	Al WIRE	Cu WIRE	SPLICE	PART NUMBER						
	DOUBLE WIRE RANGE		SINGLE WIRE RANGE									
DRAWING IS A CONTROLLED DOCUMENT.					TE TE Connectivity							
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:								NAME		
		DWN R.GRZYBOWSKI24JUN97 CHK M.S.FEHER24JUN97 APVD N.E.NEFF24JUN97 PRODUCT SPEC 108-2012 APPLICATION SPEC 114-2046 3										
		0 PLC ± - 1 PLC ± - 2 PLC ± 0.25[.010] 3 PLC ± - 4 PLC ± - ANGLES ± 5°			TAB, 6.30[.250] CONNECTING, MAG-MATE -							
L -MILLED BRASS		SEE TABLE			SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO				
					A2	00779	C-2232555	-				
CUSTOMER DRAWING					SCALE	6:1		SHEET				
						1 of 1		REV C3				