



WARNING - THIS DOCUMENT CONTAINS TECHNOLOGY WHOSE EXPORT IS RESTRICTED BY THE EXPORT ADMINISTRATION REGULATIONS ("EAR") PURSUANT TO 15 C.F.R. PARTS 730-774. VIOLATIONS OF THE EAR ARE SUBJECT TO SEVERE CRIMINAL PENALTIES UNDER THE EXPORT CONTROL REFORM ACT, AS AMENDED (TITLE 50, U.S.C., SEC. 480I, ET SEQ.).

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	R	REV PER ECN-24-287091	01OCT2024	LP	JS


1. USE INSTRUCTION SHEET 2299-5.
2. FERRULE, CONTACT AND PLUG ASSEMBLY PACKAGED UNASSEMBLED.




225554-6



225554-7
(SAME AS 225554-6, EXCEPT AS SHOWN)



225554-6
NO SCALE



225554-7
NO SCALE

SHELLS	BRASS PER ASTM B16	SILVER PLATE PER ASTM B700
DIELECTRICS	PTFE FLUOROCARBON PER ASTM-D-1457	-
GASKETS AND O-RING	SILICONE RUBBER PER A-A-59588	-
OUTER CONTACT	BeCu PER ASTM B196	SILVER PLATE PER ASTM B700
CENTER CONTACT, TCN	BeCu PER ASTM B196	GOLD PLATE PER ASTM B488 OVER NICKEL PLATE PER SAE-AMS-QQ-N-290
CONTACT, RT ANG	BRASS PER ASTM B16	GOLD PLATE PER ASTM B488 OVER NICKEL PLATE PER SAE-AMS-QQ-N-290
CRIMP FERRULE	COPPER OR BRASS ALLOY ROCKWELL B 45 MAX	SILVER PLATE PER ASTM B700
INNER FERRULE	BRASS PER ASTM B16 OR B36	SILVER PLATE PER ASTM B700
COLLAR	BRASS PER ASTM B16	SILVER PLATE PER ASTM B700
WASHER	BRASS PER ASTM B36	SILVER PLATE PER ASTM B700
COMPONENT	MATERIAL	FINISH

RECOMMENDED CABLE PREPARATION

220015-1	225554-7 & AMP	RG-225/U	225554-7
220045-2	225554-6 & AMP	RG-142/U, 142A/U & 142B/U; RG400	225554-6
CRIMP TOOL	STAMPING	CABLE	PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN P. PACHAIYAPPAN 13SEP2024 CHK J. A. BAKER 13SEP2024 APVD JAMES SLUSSER 13SEP2024	NAME PLUG, RIGHT ANGLE, WEATHERPROOF, TNC
DIMENSIONS: mm [in]		PRODUCT SPEC 108-12001	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC 408-2299-5	
MATERIAL -		WEIGHT -	RESTRICTED TO -
CUSTOMER DRAWING		SIZE A 00779 C=225554	SCALE 5:1 SHEET 1 OF 1 REV R