


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			B	ECR-18-008503	06JUN18	TF	CW
			C	ECR-18-010356	04JUL18	TF	CW
			D	ECR-19-009031	14JUN19	TF	CW
			D1	ECR-19-015632	17OCT19	TF	CW





ITEM	MATERIAL	FINISH
①	COPPER ALLOY	NICKEL UNDER PLATE ALL OVER CONTACT AREA ; Au(0.3um, 0.76um) SOLDER TINE AREA ; TIN PLATE
②	ZINC	NICKEL PLATING
③	STEEL t0.25	NICKEL PLATE OVER COPPER UNDERPLATE
④	THERMO-PLASTIC(UL:94V-0)	COLOR; BLACK
⑤		
⑥	COPPER ALLOY	TIN PLATE OVER NICKEL UNDERPLATE

- NOTES:
- RECOMMENDED SCREW SIZE ; M2.6 PANHEAD SCREW(L=5)
 - RECOMMENDED P.C BOARD THICKNESS ; 1.6mm (REF)
 - INSERTION FORCE OF RETENTION LEG TO P.C.B; 21.56N(2.2kgf) MAX/CONNECTOR.
 - RETENTIVITY OF RETENTION LEG TO P.C.B :
- 4.1 RETENTION LEG USE STAMPING PART RETENTIVITY 4.9N(0.5kgf) MIN/CONNECTOR.
- 4.2 RETENTION LEG USE TURING PART RETENTIVITY 100N(10kgf) MIN/CONNECTOR.




24	42.8	42.50	52.40	46.50	35.48	30.48	0.76um	50	5-2271085-4
9	23.8	23.45	33.35	27.45	16.43	11.43	0.76um	20	2-2271085-4
6	19.9	19.64	29.54	23.64	12.62	7.62	0.76um	14	1-2271085-4
6	19.9	19.64	29.54	23.64	12.62	7.62	0.3 um	14	1-2271085-3
24	42.8	42.50	52.40	46.50	35.48	30.48	0.76um	50	5-2271085-2
17	33.9	33.61	43.51	37.61	26.59	21.59	0.76um	36	4-2271085-2
12	27.6	27.26	37.16	31.26	20.24	15.24	0.76um	26	3-2271085-2
9	23.8	23.45	33.35	27.45	16.43	11.43	0.76um	20	2-2271085-2
6	19.9	19.64	29.54	23.64	12.62	7.62	0.76um	14	1-2271085-2
24	42.8	42.50	52.40	46.50	35.48	30.48	0.3 um	50	5-2271085-1
17	33.9	33.61	43.51	37.61	26.59	21.59	0.3 um	36	4-2271085-1
12	27.6	27.26	37.16	31.26	20.24	15.24	0.3 um	26	3-2271085-1
9	23.8	23.45	33.35	27.45	16.43	11.43	0.3 um	20	2-2271085-1
6	19.9	19.64	29.54	23.64	12.62	7.62	0.3 um	14	1-2271085-1
N	F	E	D	C	B	A	Au PLT.	POSITION	PART NO.



THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN HAO WANG 22APR14	TE Connectivity				
				CHK KOBBY ZHAO 22APR14					
				APVD XIANG XU 22APR14	NAME				
				PRODUCT SPEC 108-5288	RECEPTACLE HDR ASSY (2.3mm) RETENTION LEG TYPE STANDARD SCSI .050				
				APPLICATION SPEC					
				WEIGHT	SIZE A2				
				CUSTOMER DRAWING	CAGE CODE 00779				
					DRAWING NO C-2271085				
					RESTRICTED TO				
					SCALE 2:1				
					SHEET 1 of 1				
					REV D1				




RECOMENDED PANEL CUTOUT
THK,2mm MAX



SECTION
A-A



SECTION
A-A



RECOMMENDED PC BOARD
MOUNTING DIMMENSION
(COMPONENT SIDE)

LEAD FREE