






A	●	●	●	○	○	○	1-2272975-4	10
A	●	●	●	○	○	○	1-2272975-3	
A	●	●	●	●	●	●	1-2272975-2	9
A	○	○	●	○	○	○	1-2272975-1	
A	●	○	○	○	○	○	1-2272975-0	
A	●	●	●	○	○	●	2272975-9	
A	○	○	○	○	●	●	2272975-8	
A	●	○	○	○	○	●	2272975-7	
A	○	○	○	○	●	○	2272975-6	
A	○	○	○	○	○	●	2272975-5	
D	○	○	○	○	○	○	2272975-4	
C	○	○	○	○	○	○	2272975-3	
B	○	○	○	○	○	○	2272975-2	
A	○	○	○	○	○	○	2272975-1	
	1	2	3	4	5	6	PART NUMBER	
	CIRCUIT NUMBER							
KEY CODE	CIRCUIT PIN-OUT							
	● INDICATES CLOSED CIRCUIT							
	○ INDICATES OPEN CIRCUIT							



A	1-2272975-3
A	1-2272975-2
A	1-2272975-1
A	1-2272975-0
A	2272975-9
A	2272975-8
A	2272975-7
A	2272975-6
A	2272975-5
D	2272975-4
C	2272975-3
B	2272975-2
A	2272975-1
KEYING CODE	PART NUMBER

NOT TOOLED
NOT TOOLED

1. 2272975-1 SHOWN. SEE TABLE FOR ADDITIONAL KEYING ARRANGEMENTS.
- 2 SECONDARY LOCK SHIPPED IN PRE-LATCHED POSITION AS SHOWN.
3. PLUG ACCEPTS MCON 1.2mm CLEAN BODY FEMALE CONTACTS FOR WIRE RANGE WITH $\varnothing$ 1.2 - 1.9 INSULATION.
4. FOR OPTIONAL WIRE DRESS SEE DRAWING 2272976.
- 5 CLOSED CIRCUIT SHOWN FOR REFERENCE. SEE CIRCUIT PIN-OUT TABLE FOR CIRCUIT AVAILABILITY.
- 6 PART NUMBER AND DATE CODE MARKED IN APPROXIMATE AREA SHOWN.
7. MATING INTERFACE SHOWN ON USCAR DRAWING, 120-S-006-1-Z03.
8. REFERENCE TE INSTRUCTION SHEET 408-32106.

- 9 SHIPPING CAP. ALL CIRCUITS CLOSED ON OUTER HOUSING. ASSEMBLY DOES NOT INCLUDE SECONDARY LOCK OR CPA
- 10 ASSEMBLY DOES NOT INCLUDE CPA. RESTRICTED SALES.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D. DRUMMOND 22SEP2014	TE Connectivity			
DIMENSIONS: mm		CHK S. MANKARYOS 22SEP2014				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD S. MANKARYOS 22SEP2014	NAME PLUG ASSEMBLY, 6 POSITION, 1.2mm MCON			
0 PLC ± 1 PLC ±0.2 2 PLC ±0.20 3 PLC ± 4 PLC ± ANGLES ± FINISH		PRODUCT SPEC - APPLICATION SPEC - WEIGHT -	SIZE A2	CAGE CODE 00779	DRAWING NO C-2272975	RESTRICTED TO
MATERIAL SEE CALLOUT		CUSTOMER DRAWING	SCALE 4:1	SHEET 1	OF 1	REV A6