





P	LTR	DESCRIPTION	DATE	DWN	APVD
	1	PRELIMINARY DRAWING	30MAY2016	AD	SH
	2	ADD DASH NUMBER	18AUG2016	AD	SH
	3	ADD PART WIHT MYLAR	14SEP2016	AD	SH

- 1 MATERIAL .CAGE -0.4MM THICK NICKEL SIVLER AOOLY.  
EMI SPRING: COPPER ALLOY;
- 2.FINISH: EMI SPRING :1.27um NICKEL PALTING OVER ALL;
- 3.MATES WITH CFP MSA COMPLIANT TRANSCIVERS.
- 4.DATUM AND BASIC DIMENSION ESTABLISHED BY CUSTOMER.
- 5.MINIMUM PC BOARD THICKNESS: SIGLE SIDE APPLICATIONS=2.99±0.10mm.  
BELLY TO BELLY APPLICATION: 3.0mm MIN.
- 6.PADS AND VIAS CHASSIS GROUND;
- 7:REFERENCE APPLICATION SOEC 114-32146,HOLE A, FOR  
RECOMMENDED DRILL HOLE DIAMETER AND PLATING THICKNESS.
- 8: DATE CODE MARKED IN APPROXIMATE AREA.



THIS PRINT IS  
**PRELIMINARY**  
UNQUALIFIED PRODUCT  
CONTACT PRODUCT ENGINEERING  
BEFORE USING THIS PRINT

WITH	2274843-4
WITHOUT	2274843-2
MYLAR TAPE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 30MAY2016 ANDY.XIF		
		CHK 30MAY2016 SEAN.HAN		
		APVD 30MAY2016 SEAN.HAN		
DIMENSIONS:		PRODUCT SPEC	NAME	
mm		108-32103	CAGE ASSEMBLY,CFP2 1XT	
		APPLICATION SPEC	PRESS FIT,EMI SPRING	
		114-32146		
MATERIAL		WEIGHT		
-		-		
		CUSTOMER DRAWING		
		SCALE 1:1	SHEET 1 OF 4	
			REV 3	

