



THE DRAWING SHOWS THE 2-DIMENSIONAL REFERENCE COMPONENT CONDITION OF THE ASSEMBLY TO IDENTIFY AND SPECIFY THE NECESSARY DIMENSIONS ONLY. THE DELIVERED PARTS MAY DEVIATE FROM THE DRAWING REGARDING THE ORIENTATION AND POSITION OF EACH COMPONENT (e.g. SLACK CABLE). SO FAR THE FUNCTIONALITY IS NOT CONCERNED.



LABEL LEGEND:



TE PN: X-2286932-Y Rev.

DD/MM/YY

2.7 kV DC

—CURRENT REV.

—DATE CODE

NOTES

1 PACKAGING:

HOUSING WRAPPED IN FOAM AND FIXED WITH RUBBER BAND.
CABLE ASSEMBLY PROTECTED BY PAPER CUSHIONS INSIDE OF
STANDARD BOX ACCORDING TE SPEC. 107-18087, 107-18064.
DAMAGED TO BE AVOIDED.

2 ELECTRICAL TEST ACCORDING TE SPECIFICATION 108-18857.

USE CURRENT REVISION ALWAYS.

MIN. 10 mm STRIPPING OF OUTER JACKET AND BRAID FOR ELECTRICAL TEST PURPOSE.

△ PRODUCT SPECIFICATION: 108-94297, 108-94451

APPLICATION SPECIFICATION: 114-94130, 114-94325

MANUFACTURING CODE:




TE PART NO., CURRENT REV. LEVEL AND DATE CODE (DD.MM.YY).

TO BE PRINTED ON LABEL (ITEM 11).
LABEL TO BE ADDED TO THE CABIN.

^ LEVER POSITION CLOSED ON DELIVERY.

5 LEVER POSITION: CLOSED ON DELIVERY

		TE Connectivity	
NAME 3 POS. HVP800, 180, 35 SQMM CABLE ASSY -			
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A	-	C-2286932	-
		SCALE 1:1	SHEET 1 OF 2
		REV G	



G							
	TE PART NO.	REV.	LENGTH L [mm]	TOL. [mm]	CODING	LEVER POSITION	
OBsolete	5-2286932-0	F	500	+30	A	TS	
OBsolete	5-2286932-1	F	1000	+30			
OBsolete	5-2286932-2	F	2000	+35			
OBsolete	5-2286932-3	F	3000	+40			
-	5-2286932-4	G	4000	+50			
-	5-2286932-5	G	5000	+60	B	TS	
OBsolete	6-2286932-0	F	500	+30			
OBsolete	6-2286932-1	F	1000	+30			
OBsolete	6-2286932-2	F	2000	+35			
-	6-2286932-3	G	3000	+40			
OBsolete	6-2286932-4	F	4000	+50	C	TS	
-	6-2286932-5	G	5000	+60			
OBsolete	7-2286932-0	D	500	+30			
OBsolete	7-2286932-1	D	1000	+30			
OBsolete	7-2286932-2	D	2000	+35			
OBsolete	7-2286932-3	D	3000	+40	D	TS	
OBsolete	7-2286932-4	D	4000	+50			
OBsolete	7-2286932-5	D	5000	+60			
OBsolete	8-2286932-0	D	500	+30			
OBsolete	8-2286932-1	D	1000	+30			
OBsolete	8-2286932-2	D	2000	+35	D	TS	
OBsolete	8-2286932-3	D	3000	+40			
OBsolete	8-2286932-4	D	4000	+50			
OBsolete	8-2286932-5	D	5000	+60			

- 1 PACKAGING:
HOUSING WRAPPED IN FOAM AND FIXED WITH RUBBER BAND.
CABLE ASSEMBLY PROTECTED BY PAPER CUSHIONS INSIDE OF
STANDARD BOX ACCORDING TO SPEC. 107-18087, 107-18064.
DAMAGED TO BE AVOIDED.
- △ ELECTRICAL TEST ACCORDING TO SPECIFICATION 108-18857.
USE CURRENT REVISION ALWAYS.
MIN. 10 mm STRIPPING OF OUTER JACKET AND BRAID FOR ELECTRICAL TEST PURPOSE.
- △ PRODUCT SPECIFICATION: 108-94297, 108-94451
APPLICATION SPECIFICATION: 114-94130, 114-94325
- △ MANUFACTURING CODE:
TE PART NO., CURRENT REV. LEVEL AND DATE CODE (DD.MM.YY),
TO BE PRINTED ON LABEL (ITEM 11).
LABEL TO BE APPLIED TO THE CABLE AFTER SUCCESSFUL ELECTRICAL TEST.
- △ LEVER POSITION: CLOSED ON DELIVERY

DIESE ZEICHNUNG IST EIN KONTROLLIERTES DOKUMENT. BEMASSUNGEN UND TOLERANZEN GEMAß GPS (ISO STANDARDS).		TOLERANCING EN ISO 8015 TOLERIERUNG EN ISO 8015	
THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONING AND TOLERANCING PER GPS (ISO STANDARDS).		DWN M. Klusova 07APR2015 CHK J. Janicka 07APR2015	
DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±	
MATERIAL		APVD R. Hort 07APR2015 PRODUCT SPEC  APPLICATION SPEC 	
FINISH		SIZE A CAGE CODE - DRAWING NO. C=2286932 RESTRICTED TO -	
CUSTOMER DRAWING		SCALE 1:1 SHEET 2 OF 2 REV G	