




(FOR BOTTOM ENTRY
OR PASS THROUGH
APPLICATIONS)

RECOMMENDED PC BOARD LAYOUT
0.20[.008] THICK STENCIL

[illegible]

FINISH	EIA TAPE WIDTH	B	A	NO.OF POSN.	PART NUMBER
--------	----------------------	---	---	----------------	----------------

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN NAGALAKSHMI K 18NOV2014		 TE Connectivity Ltd.	
		CHK OLSON JOSEPH 18NOV2014			
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
		APVD OLSON JOSEPH 18NOV2014		AMPMODU REC ASSY MOD IV, DBL ROW, DUAL ENTRY,	
		PRODUCT SPEC		.100X.100CL, SMT, W/O CAP	
		108-25022		-	
		APPLICATION SPEC			
4 PLG ± - 4 PLG ± - ANGLES ± -		114-25018		SIZE	CAGE CODE
MATERIAL		WEIGHT -		DRAWING NO	
				RESTRICTED TO	
FINISH				A2 00779 C-2267178	
SEE TABLE		CUSTOMER DRAWING		SCALE	SHEET
				4:1	1 of 2
				REV	B

4

3

2

1

©

–

TE Connectivity. All Rights Reserved.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	–	SEE SHEET 1	–	–	–

1

HOUSING: FLAME RETARDANT, GLASS FILLED, POLYESTER, COLOR: BLACK, CONTACT: PHOSPHOR BRONZE,

2

CONTACT: DUPLEX PLATED 0.76μm[.000030] GOLD IN CONTACT AREA, 3.81–7.62μm[.000150–.000300] BRIGHT TIN–LEAD ON, LEADS, ALL OVER 1.27μm[.000050] MINIMUM NICKEL.

3

THESE DIMENSIONS PERTAIN TO CAVITY CENTERLINES ONLY NOT TO CONTACT LOCATIONS.

4

MARK PART NUMBER AND DATE CODE, IN APPROXIMATE LOCATION SHOWN, EITHER SIDE.

5

TOLERANCE IS NON–CUMULATIVE.

6

2 POSITION DATE CODE IS MARKED OPPOSITE SIDE OF TE CONNECTIVITY LOGO.

7

POINT OF MEASUREMENT DIMENSION FOR PLATING THICKNESS (INSIDE CONTACT BEAM).

8

POINT–OF–CONTACT DIMENSION.

9

ROHS 2002/95/EC COMPLIANT.

10

PACKAGED IN TAPE & REEL PER EIA 481 SPECIFICATION.

11

TE CONNECTIVITY TRADEMARK AND CSA LOGO ARE MOLDED INTO HOUSING.

12

NO PART NUMBER REQUIRED ON THIS PART.

13

CONTACT: DUPLEX PLATED 0.76μm[.000030] GOLD IN CONTACT AREA, 3.81–7.62μm[.000150–.000300] MATTE TIN ON LEADS, ALL OVER 1.27μm[.000050] MINIMUM NICKEL.

14

PRELIMINARY – NOT RELEASED FOR PRODUCTION

12

12

12

12

12

12

6

13

9

120mm

88mm

72mm

44mm

24mm

FINISH

EIA TAPE WIDTH

B

A

NO.OF POSN.

PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

0

PLC

±

–

1

PLC

±

–

2

PLC

±

0.13[.005]

3

PLC

±

–

4

PLC

±

–

ANGLES

±

–

FINISH

SEE TABLE

1

1

18NOV2014

NAGALAKSHMI K

18NOV2014

OLSON JOSEPH

18NOV2014

OLSON JOSEPH

18NOV2014

OLSON JOSEPH

PRODUCT SPEC

108–25022

APPLICATION SPEC

114–25018

WEIGHT

–

CUSTOMER DRAWING

SCALE 4:1

SHEET 2 OF 2

REV B

TE

TE Connectivity Ltd.

NAME

AMPMODU REC ASSY MOD IV, DBL ROW, DUAL ENTRY, .100X.100CL, SMT, W/O CAP

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A2

00779

C=2267178

–

1471–9 (1/15)