





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
GP	00		A	RELEASED	09MAY2016	Y. K	D. T
			B	REVISED PER ECO-20-008552	02JUL2020	AP	RP




- 1 HOUSING: THERMOPLASTIC, UL 94V-0, BLACK.  
CONTACTS: COPPER ALLOY.
- 2 CONFORMS TO REQUIREMENTS OF TE PRODUCT SPECIFICATION 108-32021 BASED ON TELCORDIA GR-1217-CORE FOR SYSTEM QUALITY LEVEL III APPLICATIONS IN CONTROLLED ENVIRONMENTS (CENTRAL OFFICE).
- 3 PLATED THRU HOLE REQUIREMENTS:  
FINISHED HOLE =  $\varnothing 0.360 \pm 0.040$   
DRILLED HOLE =  $\varnothing 0.450 \pm 0.025$   
COPPER THICKNESS = 0.025 MIN.  
IMMERSION TIN IF APPLICABLE = 0.0006-0.0011
- 4 PLATED THRU HOLE DIMENSIONS APPLY TO THE TOP 1.25 OF THE PCB THICKNESS FROM THE CONNECTOR MOUNTING SIDE.
- 5 DATUMS AND BASICS DIMENSIONS ESTABLISHED BY CUSTOMER.
- 6 CONNECTOR MARKED WITH PART NUMBER, DATE CODE, AND "85 OHM" IN APPROXIMATE AREA SHOWN.

160	TIN	2290193-1
SIGNAL CONTACT QTY REF	PRESS-FIT TAIL PLATING	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Y. KODAIRA 09MAY2016	TE Connectivity	
DIMENSIONS:		CHK D. TROUT 09MAY2016		
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD D. TROUT 09MAY2016	NAME	HEADER ASSY, 8 PAIR 10 COLUMN, OPEN END WALL, 85 OHM P/C, STRADA WHISPER
	0 PLC ± 1 PLC ± 2 PLC ±0.10 3 PLC ± 4 PLC ±	PRODUCT SPEC	SIZE	CAGE CODE
	ANGLES ±	APPLICATION SPEC	DRAWING NO	RESTRICTED TO
MATERIAL	FINISH	WEIGHT	A100779	C=2290193
CUSTOMER DRAWING		SCALE	5:1	SHEET 1 OF 2
		REV	B	

LOC		DIST		REVISIONS				
GP		00		P	LYR	DESCRIPTION		DATE
						SEE SHEET 1		



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	TE Connectivity	
		CHK		
DIMENSIONS:		APVD	NAME	
mm		PRODUCT SPEC	HEADER ASSY, 8 PAIR 10 COLUMN, OPEN END WALL, 85 OHM P/C, STRADA WHISPER	
		APPLICATION SPEC	SIZE	
			A1	
			CAGE CODE	
			2290193	
			DRAWING NO	
			2	
			SHEET	
			2	
			OF	
			2	
			REV	
			B	
			SCALE	
			NTS	
			CUSTOMER DRAWING	