






REVISIONS					
P	LYR	DESCRIPTION	DATE	DWN	APVD
B		REV. PER ECR-19-01395	09SEP19	D.Z	W.W
B1		ECN-21-12486	03NOV21	A.C	J.Y
B2		ECN-24-290855	28OCT24	A.C	C.P
B3		ECN-25-310312	08MAR25	A.C	C.P



SCALE 5:1



- 1 NOSE CONE - NYLON, COLOR: SEE TABLE, 30% GLASS FILLED.
DIELECTRIC - POLYESTER PCT, NATURAL, 30% GLASS FILLED.
PIN CONTACT - BRASS.
OUTER SHELL - ZINC.
- 2 PIN CONTACT - 0.38 µm MIN GOLD ON INTERFACE END.
2.5 µm MIN TIN ON SOLDER END.
BOTH OVER 1.3 µm MIN NICKEL.
OUTER SHELL - 2.0 µm MIN TIN OVER 1.52 µm MIN NICKEL.
BOTH OVER 2.54 µm MIN COPPER.
- 3 MASS = 3.94g (REFERENCE)
- 4 VACUUM PICKUP AREA.
- 5 ROAD VEHICLES 50 Ohm RADIO FREQUENCY INTERFACE.
- 6 PACKAGING: TAPE AND REEL.



PER DETAIL Z	WATER BLUE	MATERIAL BRASS	MATERIAL PCT	MATERIAL ZINC ALLOY	Z	2-2291392-0
PER DETAIL N	PASTEL GREEN				N	1-2291392-3
PER DETAIL M	PASTEL ORANGE				M	1-2291392-2
PER DETAIL L	CARMINE RED				L	1-2291392-1
PER DETAIL K	CURRY				K	1-2291392-0
PER DETAIL I	BEIGE				I	2291392-9
PER DETAIL H	HEATHER VIOLET				H	2291392-8
PER DETAIL G	BLUE GREY				G	2291392-7
PER DETAIL F	NUT BROWN				F	2291392-6
PER DETAIL E	LEAF GREEN				E	2291392-5
PER DETAIL D	CLARET VIOLET				D	2291392-4
PER DETAIL C	SIGNAL BLUE				C	2291392-3
PER DETAIL B	CREAM				B	2291392-2
PER DETAIL A	JET BLACK				A	2291392-1
CODING DETAIL	4 NOSE CONE COLOR	3 CENTER PIN	2 DIELECTRIC	1 DIE CASTING	CODING REF	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A.CAI	03NOV2021	TE Connectivity		
DIMENSIONS:		CHK C.PAN	03NOV2021			
mm		APVD J.YIN	03NOV2021	NAME MALE ASSEMBLY, STANDOFF 1 POSITION, PCB, FAKRA		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC		SIZE		
0 PLC ±0.3		108-32058		CAGE CODE		DRAWING NO
1 PLC ±0.20		APPLICATION SPEC		DRAWING NO		RESTRICTED TO
2 PLC ±		WEIGHT		00779		REV
3 PLC ±		CUSTOMER DRAWING		SCALE		10:1
4 PLC ±		SHEET		1		OF 2
ANGLES		REV		B3		
FINISH						
-						

