





LOC	DIST	REVISIONS						
		P	LTR	DESCRIPTION		DATE	DWN	APVD
GP	00		A	RELEASED		09MAY2016	Y. K.	D. T.
			B	REVISED PER ECO-17-013331		12SEP2017	JM	DT
			C	REVISED PER ECO-20-008552		02JUL2020	AP	RP



- 1 HOUSING:THERMOPLASTIC, UL 94V-0, BLACK.
CONTACTS: COPPER ALLOY.
- 2 CONFORMS TO REQUIREMENTS OF TE PRODUCT SPECIFICATION 108-32021 BASED ON TELCORDIA GR-1217-CORE FOR SYSTEM QUALITY LEVEL III APPLICATIONS IN CONTROLLED ENVIRONMENTS (CENTRAL OFFICE).
- 3 PLATED THRU HOLE REQUIREMENTS:
FINISHED HOLE = $\varnothing 0.360 \pm 0.040$
DRILLED HOLE = $\varnothing 0.450 \pm 0.025$
COPPER THICKNESS = 0.025 MIN.
IMMERSION TIN IF APPLICABLE = 0.0006-0.0011
- 4 PLATED THRU HOLE DIMENSIONS APPLY TO THE TOP 1.25mm OF THE PCB THICKNESS FROM THE CONNECTOR MOUNTING SIDE.
- 5 DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.
- 6 CONNECTOR MARKED WITH PART NUMBER, DATE CODE, AND "85 OHM" IN APPROXIMATE AREA SHOWN

128	TIN	2274731-1
SIGNAL CONTACT QTY REF	PRESS-FIT TAIL PLATING	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Y. KODAIRA 09MAY2016	TE Connectivity	
DIMENSIONS:		CHK D. TROUT 09MAY2016		
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD D. TROUT 09MAY2016	NAME	
	0 PLC ±	PRODUCT SPEC	HEADER ASSEMBLY, 8 PAIR 8 COLUMN, OPEN END WALL, 85 OHM P/C, STRADA WHISPER	
	1 PLC ±	APPLICATION SPEC		
	2 PLC ±0.10			
	3 PLC ±			
	4 PLC ±		SIZE CAGE CODE DRAWING NO	
	ANGLES ±		A100779C=2274731	
MATERIAL	FINISH SEE TABLE	WEIGHT	RESTRICTED TO	
-	1	-	CUSTOMER DRAWING	
		SCALE 5:1	SHEET 1 OF 2	REV C

