






LOC		DIST		REVISIONS						
GP		00		P	LTR	DESCRIPTION	DATE	DWN	APVD	
					A	RELEASED	09MAY2016	Y. K	D. T	
					B	REVISED PER ECR-17-013331	rev.date.2	JM	DT	

- 1
- HOUSING: THERMOPLASTIC, BLACK.
CONTACTS: COPPER ALLOY.
- 2
- CONFORMS TO REQUIREMENTS OF TE PRODUCT SPECIFICATION 108-32021 BASED ON TELCORDIA GR-1217-CORE FOR SYSTEM QUALITY LEVEL III APPLICATIONS IN CONTROLLED ENVIRONMENTS (CENTRAL OFFICE).
- 3
- PLATED THRU HOLE REQUIREMENTS:
FINISHED HOLE = $\varnothing 0.32 \pm 0.05$
DRILLED HOLE = $\varnothing 0.400 \pm 0.025$
COPPER THICKNESS = 0.025 MIN.
IMMERSION TIN IF APPLICABLE = 0.0006-0.0011
- 4
- PLATED THRU HOLE DIMENSIONS APPLY TO THE TOP 1.25mm DEPTH FROM MOUNT SIDE OF PC BOARD.
- 5
- DATUMS AND BASICS DIMENSIONS ESTABLISHED BY CUSTOMER.
- 6
- CONNECTOR MARKED ON EITHER SIDE OF HOUSING WITH PART NUMBER AND DATE CODE IN APPROXIMATE AREA SHOWN.



TIN	2274854-1
PRESS-FIT TAIL PLATING	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Y. KODAIRA 09MAY2016	TE Connectivity	
DIMENSIONS:		CHK D. TROUT 09MAY2016		
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD D. TROUT 09MAY2016	NAME HEADER ASSEMBLY, 4 PAIR 6 COLUMN, 85 OHM PIC, STRADA WHISPER	
	0 PLC ±	PRODUCT SPEC	SIZE	
	1 PLC ±	APPLICATION SPEC	CAGE CODE	
	2 PLC ±	WEIGHT	DRAWING NO	
	3 PLC ±	CUSTOMER DRAWING	RESTRICTED TO	
	4 PLC ±		A100779	
	ANGLES		C=2274854	
MATERIAL	FINISH		SCALE	
			5:1	
			SHEET	
			1 OF 2	
			REV	
			B	

