




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	ADD 1-2 AND FORMAL RELEASED	28JUN2019	IT	SH


1. MATERIAL :CAGE :0.4MM THICK NICKEL SILVER ALLOY;
EMI SPRING: COPPER ALLOY;
HEAT SINK CLIP: STAINLESS STEEL;
HEAT SINK:ALUMINUM ALLOY;
2. FINISH: EMI SPRING :1.27um NICKEL PALTING OVER ALL;
HEAT SINK:BLACK ANODIZED COATING;
HEAT SINK CLIP:PASSIVATE;
- 3.MATES WITH CFP MSA COMPLIANT TRANSCEIVERS.
- 4.DATUM AND BASIC DIMENSION ESTABLISHED BY CUSTOMER.
- 5.MINIMUM PC BOARD THICKNESS: SIGLE SIDE APPLICATIONS=2.99±0.63mm.
BELLY TO BELLY APPLICATION: 3.0mm MIN.
- 6.PADS AND VIAS CHASSIS GROUND;
- 7:REFERENCE APPLICATION SOEC 114-32146,HOLE A, FOR
RECOMMENDED DRILL HOLE DIAMETER AND PLATING THICKNESS.
- 8 :DATE CODE LOCATED AT APPROXIMATE AREA.



1-2293277-4 3D VIEW
SCALE 2:1




1-2293277-4 AS SHOWN




WITHOUT	1-2293277-5
WITH	1-2293277-4
WITHOUT	1-2293277-2
MYLAR TAPE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN ADNY.XIE 14SEP2016	TE Connectivity			
		CHK SEAN.HAN 14SEP2016				
		APVD SEAN.HAN 14SEP2016	NAME HARD WEARE KITS,CAGE,HS CFP2 1X1			
DIMENSIONS:		PRODUCT SPEC	SIZE			
mm		108-32103	CAGE CODE			
		APPLICATION SPEC	DRAWING NO			
		114-32146	RESTRICTED TO			
MATERIAL		WEIGHT	A2			
TBD		-	C=2293277			
		-	SCALE 1:1			
			SHEET 1 OF 5			
			REV A			

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-





1-2293277-2 3D VIEW
SCALE 3:2





1-2293277-5 3D VIEW
SCALE 3:2

1-2293277-2 AS SHOWN



23.35±0.25
(WITHOUT MODULE
INSERTED)


1-2293277-5 AS SHOWN





(17.00)
(STANDOFF TO HS TIP,
AFTER MODULAR INSERTED)


SECTION E-E
SCALE 2:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN ADNY.XIE 14SEP2016	TE Connectivity			
		CHK SEAN.HAN 14SEP2016				
		APVD SEAN.HAN 14SEP2016	NAME HARD WEARE KITS,CAGE,HS CFP2 1X1			
DIMENSIONS: mm		PRODUCT SPEC 108-32103	SIZE A2		CAGE CODE -	DRAWING NO C-2293277
		APPLICATION SPEC 114-32146	RESTRICTED TO -			
MATERIAL TBD		WEIGHT -	SCALE 1:1		SHEET 2 OF 5	REV A
		CUSTOMER DRAWING				





THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN ANDY.XIE 14SEP2016	<div> TE Connectivity</div>			
		CHK SEAN.HAN 14SEP2016				
		APVD SEAN.HAN 14SEP2016				
		PRODUCT SPEC -				
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME HARD WEARE KITS,CAGE,HS CFP2 1X1		
mm		0 PLC ±0.10 1 PLC ±0.10 2 PLC ±0.10 3 PLC ±0.10 4 PLC ±0.05 ANGLES ±1 FINISH		SIZE A2		
MATERIAL SEE NOTES		SEE NOTES		CAGE CODE -		
				DRAWING NO C-2293277		
				RESTRICTED TO -		
				SCALE 4:1		
				SHEET 4 OF 5		
				REV A		



THIS DRAWING IS UNPUBLISHED.
RELEASED FOR PUBLICATION
20
ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN ANDY.XIE 14SEP2016	TE Connectivity			
DIMENSIONS:		CHK SEAN.HAN 14SEP2016				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD SEAN.HAN 14SEP2016	NAME HARD WEARE KITS,CAGE,HS CFP2 1X1			
mm		PRODUCT SPEC	-			
0 PLC ±		APPLICATION SPEC	-			
1 PLC ±0.25		WEIGHT	-			
2 PLC ±0.13		CUSTOMER DRAWING	SCALE 5:1 SHEET 5 OF 5 REV A			
3 PLC ±0.1						
4 PLC ±0.05						
ANGLES ±1						
FINISH						
MATERIAL						
-						
-						