








PROJECT NO.:		REVISIONS				
P	LTR	ÄNDERUNGEN DESCRIPTION BESCHREIBUNG	DATE	DWN	APVD	
	A	NEW DRAWING	23MAY2014	R.W. Thiel		
	A1	RADII	28JUL2014	AW	Thiel	



- 1 CHARACTERS ACCORDING TO DIN 1451
CHARACTERS 1.0 RECEDE 0.15 ZONE RECEDE 0.0 OR
CHARACTERS 1.0 RAISED 0.15 ZONE RECEDE 0.2
- 2 CONTACT CAVITY NUMBER: CHARACTERS 2.5 RECEDE 0.3
- 3 ALLOWED WARPAGE +0.2/-0.3
- 4 ALLOWED WARPAGE -0.5
- 5 BULK PACKAGED
- 6 DEVIATION FOR PARTS FROM OLD MOLDS ALLOWED
- 7 PASSENDE GEGENSTUECKE SIND: Z.B. 1813271, 1823679...



- 1 MITTELSCHRIFT NACH DIN 1451
SCHRIFTHOEHE 1.0 VERTIEFT 0.15 FELD VERTIEFT 0.0 ODER
SCHRIFTHOEHE 1.0 ERHABEN 0.15 FELD VERTIEFT 0.2
- 2 KONTAKTKAMMERNUMMER: SCHRIFTHOEHE 2.5 VERTIEFT 0.3
- 3 ZULAESSIGER VERZUG +0.2/-0.3
- 4 ZULAESSIGER VERZUG -0.5
- 5 VERPACKT ALS SCHUETTUT
- 6 ABWEICHUNG FUER TEILE AUS ALTWERKZEUGEN ZULAESSIG
- 7 SUITABLE MATCHING PARTS COULD BE E.G. 1813271, 1823679...



TOLERANCES UNLESS OTHERWISE SPECIFIED ACC. TO ISO 14405 AND DIN 36742 TGG.		2282467-1		A	BLACK	3POS, HSG, DELETE CAP, SEALED	PBT-GF20	1	
THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONING AND TOLERANCING PER GPS (ISO STANDARDS).		PART-NO		REV	COLOR	DESCRIPTION	MATERIAL	ITEM NO	
DIMENSIONS: MASSENHEITEN: mm		DWN R.Wienziens 21MAY2014		CHK F.Thiel 21MAY2014	TE Connectivity				
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±, 1 PLC ±, 2 PLC ±, 3 PLC ±, 4 PLC ±, ANGLES/CHUNKEL ±, FINISH/BOHRERFLÄCHE/FARBEN -		NAME		3 POSN, HSG, DELETE CAP, SEALED 3POLIG, BLINDGEHAEUSE, GEDICHTET					
MATERIAL SEE TAB.		PRODUCT SPEC 108-18179		APPLICATION SPEC VERABREITUNGSSPEZ.		SIZE A1	CAGE CODE -	DRAWING NO. 2282467	RESTRICTED TO NUR FUER -
		WEIGHT GEWICHT -		Customer Drawing		SKUNDENZEICHNUNG		SCALE MASSSTAB 2:1	SHEET BLATT 1 OF VON 1 REV A1