







REVISIONS				
P	LTR	DESCRIPTION	DATE	DWN APVD
	A1	REVISE	22JUL2020	J.Y E.J
	A2	ADD 3 LAYER PLATING	22APR2025	C.L W.Z




1. TERMINAL DESIGNED TO BE USED WITH FLR CABLE
2. MAX. 9 TERMINAL MISSING PER REEL PERMITTED
3. 3 LOOSE SPLICES PER REEL PERMITTED
- 4 WIRE SIZE MARK,PLEASE SEE TABLE
- 5 LOW INSERTION VERSION
- 6 PRELIMINARY. NOT COMPLETE PRODUCT VALIDATION



1-2296537-3		1	1.0~1.5mm2	1.9~2.4mm	L	CuNiSi	PRE-TIN	3.4	2.0	6.4	1.5	2.7	2.8	2.25	3.6	3.7
1-2296537-2		1	0.5~0.75mm2	1.4~1.9mm	M			3.2	1.8	6.0	1.1	2.0	2.2	1.6	2.8	2.9
1-2296537-1		1	0.22~0.35mm2	1.1~1.4mm	S			2.9	2.0	6.0	-	1.8	1.8	1.3	2.35	2.5
2296537-3	A	1.0~1.5mm2	1.9~2.4mm	L	CuNiSi	PRE-TIN	3.4	2.0	6.4	1.5	2.7	2.8	2.25	3.6	3.7	
2296537-2	A	0.5~0.75mm2	1.4~1.9mm	M			3.2	1.8	6.0	1.1	2.0	2.2	1.6	2.8	2.9	
2296537-1	A	0.22~0.35mm2	1.1~1.4mm	S			2.9	2.0	6.0	-	1.8	1.8	1.3	2.35	2.5	
PART NUMBER	REV.	WIRE RANGE	INSULATION RANGE	WIRE SIZE MARK	MATERIAL	FINISH	A	B	C	D	E	F	G	H	J	
							LENGHT			WIRE CRIMP			INSULATION CRIMP			

REELING DIRECTION



SCALE 5:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN G.ZHANG 21DEC2017	TE TE Connectivity	
DIMENSIONS:		CHK E.JIANG 21DEC2017		
mm		APVD L.YIN 21DEC2017		
		PRODUCT SPEC 108-101626		
MATERIAL -		APPLICATION SPEC 116-101043	NAME FEMALE TERMINAL, TIN PLATED, REM MONO 1.2, CLEAN BODY	
FINISH -		WEIGHT -	SIZE A1 CAGE CODE - DRAWING NO C=2296537	
		CUSTOMER DRAWING	RESTRICTED TO -	
		SCALE 16:1	SHEET 1 OF 1 REV A2	