

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
B		REVISED PER ECR-16-015841	09NOV2016	SC	BW

21.6 MAX
0.5 MAX CUT OFF TAB LENGTH
6.0
0.5 MAX CUT OFF TAB LENGTH

5.6
MATE WITH 0.8mm THK TAB

SECTION G-G
SCALE 8:1

G
3.2
3.2
C
D

2.3
2.1

SECTION C-C
SCALE 10:1

3.5
3.9

SECTION D-D
SCALE 10:1

NOTE;

- CONTINUOUS STRIP ON REELS
- APPLICABLE WIRE RANGE: AWG #22~#20 (0.34~0.53mm²)
2x AWG #22 (2x0.34mm²)
- APPLICABLE INSULATION DIAMETER: ϕ 1.56~2.15mm
2x ϕ 1.95mm MAX
- MATING TAB ACCORDING TO UL310 AND IEC61210 NORM.
(WIDTH*THICKNESS 4.8*0.8mm)
- DO NOT USE WITH A HOUSNIG AS NON-INSULATION SUPPORT

2297529-1

PN

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
STAINLESS STEELTOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC \pm -
1 PLC \pm -
2 PLC \pm \pm 0.4
3 PLC \pm -
4 PLC \pm -
ANGLES \pm -
FINISH -

DWN SC KIM 26NOV2015

CHK BH CHO 26NOV2015

APVD BW KANG 26NOV2015

PRODUCT SPEC

108-61158

APPLICATION SPEC

114-61066

WEIGHT -

CUSTOMER DRAWING

TE Connectivity

NAME
187 P-LOCK REC MK-11
FOR 0.8T TAB, HEAT RESISTANT

SIZE CAGE CODE DRAWING NO RESTRICTED TO

A300779 C-2297529

SCALE 5:1 SHEET 1 OF 1 REV B

1470-19 (3/13)