



CODINGS
SHOWN WITHOUT LEVER - 1:1

THE DRAWING SHOWS THE 2-DIMENSIONAL REFERENCE COMPONENT CONDITION OF THE ASSEMBLY TO IDENTIFY AND SPECIFY THE NECESSARY DIMENSIONS ONLY. THE DELIVERED PARTS MAY DEViate FROM THE DRAWING REGARDING THE ORIENTATION AND POSITION OF EACH COMPONENT (e.g. SLACK CABLE), SO FAR THE FUNCTIONALITY IS NOT CONCERNED.



REVISIONS						
P	LYR	DESCRIPTION	DATE	DWN	APVD	
B2		NOTES AND LABEL LEGEND UPDATED	08OC12018	JM	JJ	
B3		NEW VARIANTS ADDED	12NOV2016	JM	JJ	
B4		OBSOLETE PNs	18OC12022	OS	JK	





A



B



1



LABEL LEGEND:




TE PN: X-2286949-Y Rev.
DD/MM/YY _____
2.7 kV DC TEST PASSED

CURRENT REV.

DATE CODE

B 4					
	TE PART NO.	REV.	LENGTH L [mm]	TOL. [mm]	CODING
OBSOLETE	1-2286949-0	B	500	+30	A
-	1-2286949-1	B	1000	+30	
OBSOLETE	1-2286949-2	B	2000	+35	
-	1-2286949-3	B	3000	+40	
OBSOLETE	1-2286949-4	B	4000	+50	B
-	1-2286949-5	B	5000	+60	
OBSOLETE	2-2286949-0	B	500	+30	
-	2-2286949-1	B	1000	+30	
OBSOLETE	2-2286949-2	B	2000	+35	C
-	2-2286949-3	B	3000	+40	
OBSOLETE	2-2286949-4	B	4000	+50	
-	2-2286949-5	B	5000	+60	
-	3-2286949-0	A	500	+30	D
-	3-2286949-1	A	1000	+30	
-	3-2286949-2	A	2000	+35	
-	3-2286949-3	A	3000	+40	
-	3-2286949-4	A	4000	+50	E
-	3-2286949-5	A	5000	+60	
-	4-2286949-0	A	500	+30	
-	4-2286949-1	A	1000	+30	
-	4-2286949-2	A	2000	+35	F
-	4-2286949-3	A	3000	+40	
-	4-2286949-4	A	4000	+50	
-	4-2286949-5	A	5000	+60	

1	1	1	1	LABEL, HELL, TYP 323, 25.4 x 95.25	10
3	3	3	3	1 POS. POWER CABLE, 50 SQMM	9
3	3	3	3	PROTEC. COVER 8 MM HV, 90 DEG. 50 SQMM	8
3	3	3	3	SINGLE WIRE SEAL, 8 MM HV, 90 DEG. 50 SQMM	7
3	3	3	3	SHIELD CRIMP FERRULE, 90 DEG	6
3	3	3	3	SHIELDING SLEEVE, 90 DEG	5
3	3	3	3	FINGER PROTECTION CAP 8 MM HV, 90 DEG.	4
3	3	3	3	HV 8 MM. DEEP DRAWN SOCKET PIN, 90 DEG., ASSEMBLY	3
3	3	3	3	HV 8 MM. DEEP DRAWN SOCKET PIN, 90 DEG., ASSEMBLY	2
1	-	-	-	3 POS. 8 MM HV, REC HSG, 90 DEG. ASSY. SEALED, COD C	1
-	1	-	-	3 POS. 8 MM HV, REC HSG, 90 DEG. ASSY. SEALED, COD C	
-	-	1	-	3 POS. 8 MM HV, REC HSG, 90 DEG. ASSY. SEALED, COD B	
-	-	-	1	3 POS. 8 MM HV, REC HSG, 90 DEG. ASSY. SEALED, COD A	
QTY 4-x	QTY 3-x	QTY 2-x	QTY 1-x	DESCRIPTION	ITEM NO

DIESE ZEICHNUNG IST EIN KONTROLLIERTES DOKUMENT. BEMASSUNGEN UND TOLERANZEN GEMAß GPS (ISO STANDARDS).		TOLERANCING EN ISO 8015 TOLERANCING EN ISO 8015	
THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONING AND TOLERANCING PER GPS (ISO STANDARDS).		DWN 0: Snajder 10MAR2015 CHK J. Janacka 10MAR2015	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±	
		APVD R. Hort 10MAR2015 PRODUCT SPEC see note 3 APPLICATION SPEC see note 3	
MATERIAL - - -		NAME 3 POS. HVP800, 90, 50 SQMM. CABLE ASSY - SIZE A - CAGE CODE - DRAWING NO C=2286949 RESTRICTED TO -	
CUSTOMER DRAWING		SCALE 1:1 SHEET 1 OF 1 REV B4	