









REVISIONS					
P.	LTR.	DESCRIPTION	DATE	DWN.	APVD.
	A	RELEASED	16JAN2018	HN	YS



- 注記
1. 嵌合相手コネクタ: 1717106
 2. **-Z-**より6mm位置で測定
 3. 本製品の取扱は、取扱説明書 NO. 411-78145-5に従うこと
- NOTE
1. MATING CONNECTOR PART NO.: 1717106
 2. MEASURED AT 6mm FROM **-Z-**
 3. HANDLING THIS PART SHOULD FOLLOW THE INSTRUCTION SHEET NO. 411-78145-5

POST TIN	POST TIN	GRAY	2297730-1
SOLDERING SIDE	CONTACT SIDE		
CONTACT FINISH		COLOR	TE PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN H. NIEDA	16JAN2018	TE TE Connectivity	
DIMENSIONS: mm		CHK Y. SHINDO	16JAN2018		
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD S. AMEMIYA	16JAN2018	NAME 0.64 12POS CAP ASSY SMT REVERSE LOCK TYPE	
	0-PLC ±0.3	PRODUCT SPEC			
	1-PLC ±0.1	APPLICATION SPEC			
	2-PLC ±0.1				
	3-PLC ±0.1	APPLICABLE		SIZE A100779	
	4-PLC ±0.001				
MATERIAL PPS GF40 BRASS		FINISH		WEIGHT 3.52g	RESTRICTED TO
				CUSTOMER DRAWING	5:1