



D




NOTES
Bemerkungen




PACKAGING: PRODUCT REELED ON CORRUGATED REEL WITH INTERLEAVING PAPER
FOUR REELS PER CORRUGATED SHIPPING BOX. QUANTITY: 3000 PCS./REEL.
Verpackung: Spulenware auf Wellpappespule mit Zwischentlagenpapier
Vier Spulen pro Versandkarton. Stückzahl: 3000 Teile/Spule.

CONDITION AS DELIVERED
Auslieferungszustand




D

C




SECTION Q-Q




C

B



B



TE CONNECTIVITY LOGO
TE Connectivity Logo



REVISION STATE AND DATE CODE
Revisionstatus und Datumcode




LISTED WEIGHT INCLUDE THE CARRIER STRIP AND THE DIELECTRIC
Gewicht inklusive Traegerstreifen und Dielektrikum



APPLICATION TOOL PN SEE IN APPLICATION SPEC, 114-94413
PN des Applicators siehe in Verarbeitungsspec. 114-94413.



ALLOWED AREA FOR CONTACT GRIPPING FOR CABLE TERMINATION
Zulaessiger Bereich zum Greifen des kontaktes bei der Kabelverarbeitung



DURING THE CABLE ASSEMBLY PROCESS, THE CONTACT MAY BE
LOADED WITH MAX. 30 N IN AXIAL DIRECTION.
THE INSERTION FORCE INTO THE HOUSING MAY NOT EXCEED 60 N.
Im Kabelmontageprozess darf der Kontakt an gezeigter
Stelle axial mit max. 30 N belastet werden.
Die Montagekraft in die Gehäusekammer darf max. 60 N betragen.



INSERTION AREA FOR GAUGE PIN DIAMETER 2,8-0,005, FORCE 10N MAX.
Einfuehrbereich fuer Pruefpin Ø 2,8-0,005, Pruefkraft 10N max.

SUB ASSEMBLY SOCKET CONTACT	SOCKET OUTER CONTACT	CuSn	Sn (1-3 µm)	A	2298494-1
	DIELECTRIC	PBT	BLUE (RAL 5012) SIMILAR		
DESCRIPTION		MATERIAL	FINISH	REV	PART No

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K.Weinberger 14NOV2017	TE Connectivity		
DIMENSIONS:		CHK G.van de Burt 14NOV2017			
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD F. Schrettlinger 14NOV2017	NAME SUBASSEMBLY SOCKET CONTACT MATE-AX 180 DEGREES, RG174		
	0 PLC ±0.2 1 PLC ±0.2 2 PLC ±0.2 3 PLC ± 4 PLC ± ANGLES ±°	PRODUCT SPEC 108-94515 APPLICATION SPEC 6	SIZE CAGE CODE DRAWING NO A1 - C=2298494		
MATERIAL - -	- -	WEIGHT 5 0.45g CUSTOMER DRAWING	RESTRICTED TO SCALE 10:1 SHEET 1 OF 1 REV A5		

A