





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD

A -

CODING A AS SHOWN




X
10:1 CPA IN PRE LOCKED POSITION






NOTES




- SUITABLE CONTACTS SEE DRAWING 928999, 963715
- PACKAGING: LOOSE PIECE IN CARDBOX
- MATING PART EXECUTION ACC. TO DRAWING WSK 013 070 BL
- MATERIAL REMOVAL OPTIONAL IN EXECUTIN AND POSITION ACC. TO MANUFACTURER POSSIBLE



CODING B



OPENING GUIDE: TO OPEN THE LOCKED CABLE FIXING. USE A Ø1x0.18MM SCREWDRIVER AND PUSH IN THE SHOWN OPENING SEE POS. 1. IN THE SHOWN OPENING IN POS. 2

2315904-2	A	B	1563253-2	B	LIGHT GREEN	6027	4POS. MQS REC. HSG. CPA GN	4	
			2315916-2	A	YELLOW	1018	4POS. MQS REC. HSG. COD B	3	
2315904-1	A	A	1563253-1	B	RED	3003	4POS. MQS REC. HSG. CPA RD	2	
			2315916-1	A	YELLOW	1018	4POS. MQS REC. HSG. COD A	1	
Assy-No	REV	CODING	PART NO	REV	COLOR	RAL-NO	DESCRIPTION	ITEM NO	
THIS DRAWING IS A CONTROLLED DOCUMENT.									
DIMENSIONS: mm			DWN V.GE 26APR2017		 TE Connectivity				
			CHK SY.W 26APR2017						
TOLERANCES UNLESS OTHERWISE SPECIFIED: 			APVD I.YIN 26APR2017		NAME				
			PRODUCT SPEC		4POS. MQS. REC HSG. ASSY				
			APPLICATION SPEC		-				
			RESTRICTED TO		-				
MATERIAL			SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO		
-			A1		00779	C=2315904	-		
CUSTOMER DRAWING							SCALE 5:1	SHEET 1 of 1	REV A