

1 ONLY THE GERMAN LANGUAGE SHALL BE BINDING
Massgebend ist der deutsche Text

2 DETAILS OF DESIGN ARE LEFT TO TE CONNECTIVITY
Einzelheiten der Ausführung bleiben TE CONNECTIVITY ueberlassen

3 PACKAGING: BULK IN CARDBOARD BOX
Verpackung: Schuettgut in Karton

4 TE ORDER NO. X-2310138-Y SEE TABLE
TE-Bestellnummer X-2310138-Y siehe Tabelle

5 CONDITION AS SUPPLIED: TPA IN PRE LOCKED POSITION
Auslieferungszustand: Sekundaersicherung in Vorraststellung



6 MATCHING TO CONTACT E.G. TE NO. 2298490 AND 2298511
Passend zu Kontakt z.B. TE-Nr. 2298490 und 2298511

7 TE ORDER NO. ACCORDING TABLE BELOW
TE Bestellnummer nach Tabelle unten


8 ALL NOT SPECIFIED INTERFACE-DIMENSIONS ACCORDING
INTERFACE DRAWING 208-18130
Alle nicht definierten Schnittstellenmasse entsprechend
Schnittstellenzeichnung 208-18130

9 SUITABLE MATING CONNECTOR TE-PN X-2310137-Y
Passender Anschlussstecker TE-PN X-2310137-Y



10 CONNECTION TESTS COMBINED WITH CONTACT LEADS ARE TO BE MA
WITH RF-ADAPTER 2318195-1
Konfektionspruefungen in Verbindung mit Leitungen sind mit
HF-Testadapter 2318195-1 durchzufuehren




VARIANT 1 - WITHOUT CLIP RAIL
2310138-1 CODING "A" AS SHOWN




SECTION A-A




SCALE 2:1





CODINGS, PLUG SIDE, SIMILARITY AS VIEW
Kodierung, Steckseite, Darstellung der Kodierungen nur ähnlich

4805 (3/13)


(CODINGS AND MISSING DIMENSIONS EQUIVALENT TO VARIANT 1)

A



SECTION B-B



SCALE 2:1






SECTION A-A

4805 (3/13)


VARIANT 3 - WITH CLIP RAIL EWCAP-005-7

4-2310138-1 CODING "A" AS SHOWN



(CODINGS AND MISSING DIMENSIONS EQUIVALENT TO VARIANT 1)




SECTION B-B



SECTION A-A



SCALE 2:1



VARIANT 3 WITH CLIP RAIL EWCAP-005-7	5-2310138-9	A	1	Z	TPA	PA66-GF30	TRAFFIC PURPLE	1.41	2
	HOUSING		1				WATER BLUE		1
	5-2310138-2	A	1	M	TPA	PA66-GF30	TRAFFIC PURPLE	1.41	2
	HOUSING		1				EMERALD GREEN		1
	5-2310138-1	A	1	L	TPA	PA66-GF30	TRAFFIC PURPLE	1.41	2
	HOUSING		1				PASTEL GREEN		1
	5-2310138-0	A	1	X	TPA	PA66-GF30	TRAFFIC PURPLE	1.41	2
	HOUSING		1				CURRY		1
	4-2310138-9	A	1	J	TPA	PA66-GF30	TRAFFIC PURPLE	1.41	2
	HOUSING		1				BEIGE		1
	4-2310138-8	A	1	H	TPA	PA66-GF30	TRAFFIC PURPLE	1.41	2
	HOUSING		1				HEATHER VIOLET		1
	4-2310138-7	A	1	G	TPA	PA66-GF30	TRAFFIC PURPLE	1.41	2
	HOUSING		1				PLATINUM GREY		1
	4-2310138-6	A	1	F	TPA	PA66-GF30	TRAFFIC PURPLE	1.41	2
	HOUSING		1				NUT BROWN	1.41	1
VARIANT	4-2310138-5	A	1	E	TPA	PA66-GF30	TRAFFIC PURPLE	1.41	2
	HOUSING		1				MAY GREEN	1.41	1
	4-2310138-4	A	1	D	TPA	PA66-GF30	TRAFFIC PURPLE	1.41	2
	HOUSING		1				CLARET VIOLET	1.41	1
	4-2310138-3	A	1	C	TPA	PA66-GF30	TRAFFIC PURPLE	1.41	2
	HOUSING		1				LIGHT BLUE	1.41	1
	4-2310138-2	A	1	B	TPA	PA66-GF30	TRAFFIC PURPLE	1.41	2
	HOUSING		1				PURE WHITE	1.41	1
	4-2310138-1	A	1	A	TPA	PA66-GF30	TRAFFIC PURPLE	1.41	2
	HOUSING		1				JET BLACK	1.41	1
	TE ORDER NO.	REV.	QTY.	COD.	DESCRIPTION	MATERIAL	COLOUR	WEIGHT [g]	POS.
	THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN Nelson.R 21MAY2018	TE Connectivity			
	DIMENSIONS:				CHK M. Schoedel 21MAY2018				
	mm				APVD E. Schrettlinger 15MAY2019				
	TOLERANCES UNLESS OTHERWISE SPECIFIED:				PRODUCT SPEC				
	0 PLC ±0.2				108-94709	NAME 1POS. MATE-AX, PIN HSG ASSY, 180DEG 1pol. MATE-AX, Stiftgeh. Zsb, 180Grad			
	1 PLC ±0.2				APPLICATION SPEC				
	2 PLC ±0.2				116-94468	SIZE CAGE CODE DRAWING NO RESTRICTED TO			
	3 PLC ±0.2				WEIGHT				
	4 PLC ±0.2				116-94468	A 00779 ©=2310138			
	ANGLES FINISH				±0°				
	MATERIAL				CUSTOMER DRAWING	SCALE 10:1 SHEET 3 OF 3 REV A1			
	-				-				