

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASE TO PRODUCTION	18 JUN 2020	AY	PS
	A1	SMART PN DETAILS ADDED	15 FEB 2022	SCB	PS
	A2	PN OBSOLETE 2316113-3/4/5	20 AUG 2025	KS	PS

- NOTES:
- 1



MATERIAL:
PHOSPHOR BRONZE, 0.2mm THICK
- 2

FINISH:
1.27-2.54 μm TIN ALL OVER
UNDERPLATE 1.27 μm MIN NICKEL ALL OVER
- 3


CONTACT AREA "A": MIN 0.1 μm THK GOLD
CRIMP AREA "C" : 1.27 - 2.54 μm THK TIN
UNDERPLATE 1.27 μm MIN NICKEL ALL OVER
- 4

CONTACT AREA "A" : MIN 0.38 μm THK GOLD
CRIMP AREA "C" : 1.27 - 2.54 μm THK TIN
UNDERPLATE 1.27 μm MIN NICKEL ALL OVER
- 5


CONTACT AREA "A" : MIN 0.76 μm THK GOLD
CRIMP AREA "C" : 1.27 - 2.54 μm THK TIN
UNDERPLATE 1.27 μm MIN NICKEL ALL OVER
6. APPLICABLE HOUSINGS :
SINGLE ROW : 2316102
DUAL ROW : 2316108, 2316109




SECTION U-U



SECTION J-J
20:1



SECTION K-K
20:1



(CRIMP UP)

WIRE RANGE: 0.08-0.22 mm² (28-24 AWG)
INSULATION RANGE: Ø1.0mm MAX

5	-	2MM-RT-M-H-LP	5-2316113-6	LOOSE PIECE - HANDTOOL
5	30,000	2MM-RT-M-H-ST	5-2316113-5	OCEAN APPLICATOR
4	-	2MM-RT-M-M-LP	4-2316113-5	LOOSE PIECE - HANDTOOL
4	30,000	2MM-RT-M-M-ST	4-2316113-4	OCEAN APPLICATOR
3	-	2MM-RT-M-F-LP	3-2316113-4	LOOSE PIECE - HANDTOOL
3	30,000	2MM-RT-M-F-ST	3-2316113-3	OCEAN APPLICATOR
2	-	2MM-RT-M-T-LP	2-2316113-3	LOOSE PIECE - HANDTOOL
2	30,000	2MM-RT-M-T-ST	2-2316113-2	OCEAN APPLICATOR
FINISH		QTY PER REEL	SMART PN	PART NUMBER
				TOOLING

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 28SEP2018 RAKSHITH R NAYAK	 TE Connectivity				
DIMENSIONS: mm		CHK RAKSHITH R NAYAK					
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD PRASHANTH S	NAME Strip layout for COSI connector SR, STRIP, PLAIN, AWG 26-30			
	0 PLC ±0.15 1 PLC ±0.10 2 PLC ±0.10 3 PLC ±0.10 4 PLC ±0.10 ANGLES ± FINISH -		PRODUCT SPEC -				
	MATERIAL SEE NOTE -		APPLICATION SPEC -	SIZE A2	CAGE CODE 00779	DRAWING NO C-C-2316113	RESTRICTED TO -
	CUSTOMER DRAWING		SCALE 5:1		SHEET 1 OF 2	REV A2	

