


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
C		AS PER ECR-19-007252	13MAY2019	CHS	JB
D		AS PER ECR-19-014752	13MAY2019	CHS	JB
D1		AS PER ECR-20-000013	02JAN2020	MS	JB
D2		AS PER ECR-20-000978	20JAN2020	HPS	JB

- NOTES
Bemerkungen
- 1 TE SINGLE PART NUMBER
TE Einzelteilnummer
 - 2 REVISION OF THE MOLD
Werkzeugänderungsindex
 - 3 MATERIAL MARKING ACCORDING TO VDA 260
Materialkennzeichnung nach VDA 260
 - 4 PRODUCTION DATE
Produktionsdatum
 - 5 MOLD CAVITY MARKING
Nestmarkierung
 - 6 CONTACT CAVITY NUMBERING
Kammernummerierung
 - 7 INTERFACE ACCORDING TO TE-SPECIFICATION 208-18037, REV.: 2
Schnittstelle gemäß TE-Spezifikation 208-18037, Rev.: 2
 - 8 DELIVERY CONDITION IN OPEN POSITION
Lieferzustand im geöffneten Zustand
 - 9 REGRIND 0% ACCORDING TO CUSTOMER REQUIREMENT
Regrind 0% gemäß Kundenanforderung
 - 10 PACKAGING: LOOSE PIECES IN BAG IN BOX
Verpackung: Schüttgut im Beutel im Karton
 - 11 TE-LOGO ACC. TE-SPEC. TEC-202-36, VERSION 1621426-5, 0.15 RAISED
TE-Logo nach TE-Spez. TEC-202-36, Ausführung 1621426-5, 0.15 erhaben



2. Kontaktsicherung geschlossen
RETAINER CLOSED

2317303-1
AS SHOWN

SCALE 2:1

NOT TOOLED	2317303-9	D		1		Water-Blue	MATenet 2x3-Port Frame, CODE Z	5
NOT TOOLED	2317303-7	D		1	PBT-GF10	Beige	MATenet 2x3-Port Frame, CODE J	4
NOT TOOLED	2317303-3	D		1		Blue	MATenet 2x3-Port Frame, CODE C	3
NOT TOOLED	2317303-2	D		1		White	MATenet 2x3-Port Frame, CODE B	2
	2317303-1	D	3.3	1	PBT-GF10	Black	MATenet 2x3-Port Frame, CODE A	1
TE ORDER-NO. TE Bestell-Nr.	REV.	WEIGHT [g]	QTY Stück	MATERIAL	COLOUR Farbe	DESCRIPTION Beschreibung	ITEM	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
SEE TABLE

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC	±3
1 PLC	±3
2 PLC	±1
3 PLC	±
4 PLC	±
ANGLES	±1°
FINISH	-

SEE TABLE

APPROVED BY: VISHNU PATAGAR
CHK: B. JOACHIM
APVD: F. CHRISTIAN

DATE: 01MAR2018
DATE: 06MAR2018
DATE: 10MAR2018

PRODUCT SPEC: 108-94771
APPLICATION SPEC: 116-94636

WEIGHT: SEE TABLE

CUSTOMER DRAWING

NAME: 2x3 PORT MATenet FRAME
MATenet.2x3 PORT FRAME

SIZE: A1
CAGE CODE: 00779
DRAWING NO: ©=2317303

RESTRICTED TO: 1
SCALE: 5:1
SHEET: 1 OF 1
REV: 02

DIMENSION AND TOLERANCES ACCORDING TO:
Bemaßungen und Toleranzen gemäß:

DIN EN ISO 8015 (A0) - DIN EN ISO 291
DIN EN ISO 14405