


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	REVISED PER ECR-24-199305	23FEB2024	AK	DS
	B	REVISED PER ECN-25-317859	11APR2025	MMK	JHW




△ MATERIAL MARK


2. RECOMMENDED WIRE RANGE:
14-16 AWG COPPER STRANDED.

3. INSULATION DIAMETER RANGE:
2.3~3.5


4. SUPPLIED CONTINUOUS ON A REEL





SECTION C-C



SECTION A - A



SECTION B-B



M2	COPPER ALLOY	2329913-1
MATERIAL MARK/1	MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN SREERAJ K R 12JAN2022		TE Connectivity	
DIMENSIONS: mm		CHK DAVID SWARTZ 12JAN2022		NAME POWER VERSA-LOCK REC TERMINAL UNSEALED 14-16 AWG	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD VINAY 12JAN2022		APPLICATION SPEC	
		PRODUCT SPEC 108-143081		RESTRICTED TO	
MATERIAL		FINISH		SIZE	
-		-		CAGE CODE	
SEE TABLE		PRE-PLATED Sn		DRAWING NO	
		WEIGHT		C-2329913	
		CUSTOMER DRAWING		SCALE	
				10:1	
				SHEET	
				1 of 1	
				REV	
				B	