






LOC	DIST	REVISIONS					
AF	-	P	LTR	DESCRIPTION	DATE	DWN	APVD
			A	FIRST RELEASED	06JUL2018	WH	DZ
			B	REVISED PER ECR-21-106594	05AUG2021	SK	DZ



57.00[2.244]	52.00[2.047]	46.2[1.819]	51.60[2.031]	24	2-2321953-4
52.80[2.079]	47.80[1.882]	42.0[1.654]	47.40[1.866]	22	2-2321953-2
48.60[1.913]	43.60[1.717]	37.8[1.488]	43.20[1.701]	20	2-2321953-0
44.40[1.748]	39.40[1.551]	33.6[1.323]	39.00[1.536]	18	1-2321953-8
40.20[1.583]	35.20[1.386]	29.4[1.157]	34.80[1.370]	16	1-2321953-6
36.00[1.417]	31.00[1.220]	25.2[.992]	30.60[1.205]	14	1-2321953-4
31.80[1.252]	26.80[1.055]	21.0[.827]	26.40[1.039]	12	1-2321953-2
27.60[1.087]	22.60[.890]	16.8[.661]	22.20[.874]	10	1-2321953-0
23.40[.921]	18.40[.724]	12.6[.496]	18.00[.709]	8	2321953-8
19.20[.756]	14.20[.559]	8.4[.331]	13.80[.543]	6	2321953-6
15.00[.591]	10.00[.394]	4.2[.165]	9.60[.378]	4	2321953-4
10.80[.425]	5.80[.228]	--	5.40[.213]	2	2321953-2
DIM D	DIM C	DIM F	DIM L	NO. OF POS	PART NO.

RECOMMENDED CUT-OUT FOR
2.00[0.079] MAX THICK PANEL

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN WARREN HUO	07FEB2018	 TE Connectivity	
		CHK WARREN HUO	08FEB2018		
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±. 1 PLC ±. 2 PLC ±0.25[0.010] 3 PLC ±. 4 PLC ±. ANGLES ±. FINISH	APVD DANIEL ZHANG	08FEB2018	NAME PANEL MOUNT PLUG HOUSING,HR VAL-U-LOK, GLOW WIRE AND VO	
		PRODUCT SPEC 108-2112			
		APPLICATION SPEC 114-13172			
MATERIAL 		WEIGHT -			
		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
		A2	00779	C-2321953	-
Customer Drawing				SCALE	N/A
				SHEET	1 OF 1
				REV	B