




NAME	CABLE ASSEMBLY, DIRECT ATTACH QSFP									
	26AWG, 25GIG									
ION SPEC										
ION SPEC	SIZE	CAGE CODE	DRAWING NO					RESTRICTED TO		
-	A1	00779	C=2333842							
CTED CUSTOMER			SCALE	5:1	SHEET	1	OF	2	REV	C2




2. SEE SHEET 2 FOR WIRING SCHEMATIC.
3. PRODUCT AND PROCESSING MUST MEET THE REQUIREMENTS OF THE SPECIFICATION TEC-138-702.
4. CABLE ASSEMBLY TO BE TESTED FOR OPENS, SHORTS AND PROPER EEPROM PROGRAM.
5. EEPROM DOES NOT INCLUDE PAGE SWAPPING.
- ⑥ TEST IN ACCORDANCE WITH IEEE802.3bj.
- ⑦ DASH NUMBER 41 THRU 48 CONFORM TO 56G, PAM-4 IEEE802.3CD PERFORMANCE REQUIREMENTS.
- ⑧ LABEL INFORMATION FOR 56 GIG PMS (-41 THRU -48): -41 SHOWN.



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-



WIRING PATTERN

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. YI	17APR2018	 TE Connectivity										
		CHK G. FRANKLIN	17APR2018											
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	CABLE ASSEMBLY, DIRECT ATTACH QSFP 26AWG, 25G1G									
mm														
	0 PLC	±		PRODUCT SPEC	-									
	1 PLC	±												
	2 PLC	±												
	3 PLC	±												
	4 PLC	±												
	ANGLES		±	APPLICATION SPEC										
MATERIAL	FINISH			SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO							
-	-			A	00779	©=2333842								
-	-			RESTRICTED CUSTOMER			SCALE	5:1	SHEET	2	OF	2	REV	C2