








0.9±0.1	0.76μm Au	24	400	NO	200	1-2327672-3
	0.38μm Au				100	1-2327672-2
	FLASH Au/PdNi				50	1-2327672-1
	0.76μm Au	20	500	YES	200	2327672-3
	0.38μm Au				100	2327672-2
	FLASH Au/PdNi				50	2327672-1
A	PLATING	POCKET TAPE PITCH	REEL QUANTITY	PICK AND PLACE TAPE	MATING CYCLES	PART NUMBER




THIS DRAWING IS A CONTROLLED DOCUMENT.		DRN M. SHIRK 22FEB2018 CHK D. HARMON 22FEB2018 D. HARMON 22FEB2018		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±. 1 PLC ±. 2 PLC ±. 3 PLC ±. 4 PLC ±. ANGLES ±. FINISH		NAME RECEPTACLE ASSEMBLY, RIGHT ANGLE, 56 POSITION, SLIVER 2.0 -	
		APVD PRODUCT SPEC 108-130021 APPLICATION SPEC 114-130008		SIZE A1	
MATERIAL 		WEIGHT -		CASE CODE 100779	
		CUSTOMER DRAWING		DRAWING NO C=2327672	
				RESTRICTED TO -	
				SCALE 10:1 SHEET 1 OF 4 REV D4	

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. SHIRK	22FEB2018	 TE Connectivity	
		CHK D. HARMON	22FEB2018		
DIMENSIONS:		APVD D. HARMON	22FEB2018	NAME RECEPTACLE ASSEMBLY, RIGHT ANGLE, 56 POSITION, SLIVER 2.0	
mm		PRODUCT SPEC			
		0 PLC	±"	SIZE A1	
		1 PLC	±"		
		2 PLC	±"		
		3 PLC	±"		
		4 PLC	±"	CAGE CODE 2327672	
		ANGLES	±"		
		FINISH	±"	DRAWING NO 114-130008	
MATERIAL		WEIGHT	-	RESTRICTED TO -	
CUSTOMER DRAWING			SCALE 10:1	SHEET 2	OF 4
				REV D4	

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



RECOMMENDED PCB OUTLINE DIMENSIONS:
TOLERANCE VALUES ARE CRITICAL. PLEASE BE SURE TO DESIGNATE
TOLERANCES TO PCB SUPPLIER TO ENSURE OPTIMIZED FUNCTIONALITY.



DETAIL J
SCALE 20:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. SHIRK	22FEB2018	TE Connectivity	
		CHK D. HARMON	22FEB2018		
DIMENSIONS:		APVD D. HARMON	22FEB2018	NAME RECEPTACLE ASSEMBLY, RIGHT ANGLE, 56 POSITION, SLIVER 2.0	
mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC	
		0 PLC ±"		108-130021	
		1 PLC ±"		APPLICATION SPEC	
		2 PLC ±"		114-130008	
		3 PLC ±"		WEIGHT	
		4 PLC ±"		-	
		ANGLES		SIZE	
		FINISH		114-130008	
MATERIAL		CUSTOMER DRAWING		SCALE	
				10:1	
				SHEET	
				3	
				OF	
				4	
				REV	
				D4	

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-

TABLE 1: CONNECTOR CONTACT IDENTIFICATION 

CONTACT NUMBER	SIDE A	SIDE B
1	GROUND	GROUND
2	SIGNAL	SIGNAL
3	SIGNAL	SIGNAL
4	GROUND	GROUND
5	SIGNAL	SIGNAL
6	SIGNAL	SIGNAL
7	GROUND	GROUND
8	SIGNAL	SIGNAL
9	SIGNAL	SIGNAL
10	GROUND	GROUND
11	SIGNAL	SIGNAL
12	SIGNAL	SIGNAL
13	GROUND	GROUND
14	SIGNAL	SIGNAL
15	SIGNAL	SIGNAL
16	GROUND	GROUND
17	SIGNAL	SIGNAL
18	SIGNAL	SIGNAL
19	GROUND	GROUND
20	SIGNAL	SIGNAL
21	SIGNAL	SIGNAL
22	GROUND	GROUND
23	SIGNAL	SIGNAL
24	SIGNAL	SIGNAL
25	GROUND	GROUND
26	SIGNAL	SIGNAL
27	SIGNAL	SIGNAL
28	GROUND	GROUND






FIGURE 1 
DIRECTION OFF TOP OF REEL
FOR USER UNREELING
SHOWN AS 2327672-1, 2327672-2 OR 2327672-3
SCALE 2:1







FIGURE 2 
DIRECTION OFF TOP OF REEL
FOR USER UNREELING
SHOWN AS 1-2327672-1, 1-2327672-2 OR 1-2327672-3
SCALE 2:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. SHIRK 22FEB2018	 TE Connectivity	
DIMENSIONS:		CHK D. HARMON 22FEB2018		
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD D. HARMON 22FEB2018	NAME RECEPTACLE ASSEMBLY, RIGHT ANGLE, 56 POSITION, SLIVER 2.0	
	0 PLC	±	PRODUCT SPEC	
	1 PLC	±	108-130021	
	2 PLC	±	APPLICATION SPEC	
	3 PLC	±	114-130008	
MATERIAL		WEIGHT	SIZE A1	CAGE CODE 00779
			DRAWING NO C=2327672	RESTRICTED TO -
			CUSTOMER DRAWING	SCALE 10:1 SHEET 4 OF 4 REV D4