





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASED	24JUNE2022	TZ	SH



- 1"TE", PART NUMBER, AND DATECODE TO BE MARKED IN AREA SHOWN.
PARTS UNDER 2.00 LONG MAY BE MARKED ON BOTH SIDES.
- 2MATERIAL:
HOUSING - GLASS FILLED HIGH TEMP THERMO PLASTIC,BLACK, UL94 V-0
SIGNAL CONTACT - COPPER ALLOY
POWER CONTACT - HIGH CONDUCTIVITY COPPER ALLOY
- 3CONTACT PLATING: NOBLE METAL PLATING ON CONTACT FUNCTIONAL AREA
OF POWER AND SIGNAL CONTACTS.
- 4MECHANICAL CONNECTOR KEEP OUT ZONE.
- 5DATUM AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.
- 6PCB - HOLE DIAMETERS ARE FINISHED HOLE SIZE.
- 7PCB - 1.15±0.025 DRILLED HOLES PLATED WITH 0.0076 MIN Sn
OVER 0.025 TO 0.076 Cu PLATING TO ACHIEVE A 1.02 ±0.05 HOLE.



16P	2334569-2
DESCRIPTION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.LU 09APR2021	TE Connectivity VERTICAL RECEPTACLE, PRESS FIT MULTI-BEAM PLUS	
DIMENSIONS:		CHK M.LU 09APR2021		
mm		APVD S.HAN 09APR2021		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC		
0 PLC ±"		108-128074	NAME	
1 PLC ±"		APPLICATION SPEC	SIZE	
2 PLC ±0.20		114-128075	CAGE CODE	
3 PLC ±0.10		WEIGHT	DRAWING NO	
4 PLC ±"		CUSTOMER DRAWING	REV	
ANGLES ±#2		SCALE	SHEET	
FINISH		1:1	OF	
MATERIAL		2	2	
1		3	A	

